

Eaton industrial network management card comparison chart

This table can be referenced to compare the Eaton Industrial Gateway cards to their predecessors, the Power Xpert Gateway cards. The X-Slot Card (P/N: INDGW-X2) replaces the Eaton Power Xpert Gateway X Slot UPS Card (P/N: PXGXUPS - EOL December 2021). The Eaton Industrial Gateway Mini-Slot Card (P/N: INDGW-M2) replaces the Eaton Power Xpert Gateway UPS Mini Slot Card (P/N: PXGMSUPS - EOL in March 2022).

Feature	PXGMSUPS	PXGXUPS	INDGW-M2	INDGW-X2
Supported UPS	93PM	9155, 9315, 9355, 9390, 9395, 9395P, 9395C, BladeUPS	5P, 5PX, 9130, 9PX, 9PXM, 9SX, 93PM, 93E	BladeUPS, 9155, 9355, 9395, 9395P, 9395C
TCP Ports	RJ45 Port	2 RJ45 Ports	RJ45 Port	RJ45 Port
Speed	10/100BaseT	10/100BaseT	10/100/1000BaseT	10/100/1000BaseT
Web-based UI	Yes	Yes	Yes	Yes
IPv4 & IPv6	Yes	Yes	Yes	Yes
USB	USB device port (used for initial network connection through a standard RNDIS)	USB device port (used for initial network connection through a standard RNDIS)	USB device port (used for initial network connection through a standard RNDIS)	USB device port (used for initial network connection through a standard RNDIS)
ModbusTCP	Yes	Yes	Yes	Yes
Modbus RTU	Yes	No	Yes	Yes
HTTP	Yes	Yes	No	No
HTTPS	Yes	Yes	Yes	Yes
BACnet/WS	Yes	Yes	Yes	Yes
BACnet/IP	Yes	Yes	Yes	Yes
BACnet BBMD	No	No	Yes	Yes
NTP	Yes	Yes	Yes	Yes
SMTP	Yes	Yes	Yes	Yes
DHCP	Yes	Yes	Yes	Yes
SNMP v1/v3	Yes	Yes	Yes	Yes
TFTP	No	No	Yes	Yes
SMTPS	No	No	Yes	Yes
BOOTP	No	No	Yes	Yes
SLAAC	No	No	Yes	Yes
SSH	No	No	Yes	Yes
MQTTS	No	No	Yes	Yes
Real Time Clock	Yes	Yes	Yes	Yes
Temperature and Humidity Sensor	Yes (116750224-001)	Yes (116750224-001)	Yes (EMPDT1H1C2)	Yes (EMPDT1H1C2)
Languages	English, Russian, Polish, Chinese, Spanish, Portuguese-Brazil, Italian, French, German	English, Russian, Polish, Chinese, Spanish, Portuguese-Brazil, Italian, French, German	English, French, German, Italian, Spanish, Chinese Simplified Chinese Traditional, Japanese, Russian	English, French, German, Italian, Spanish, Chinese Simplified Chinese Traditional, Japanese, Russian

For more information, visit Eaton.com/NetworkManagement