



SMART1200XLHG Estimated Runtime

UPS	Battery Pack	BP Qty.	Load in Watts													
			50	100	150	200	300	350	400	450	500	550	600	650	700	750
SMART1200XLHG	Internal batteries	1	231	122	80	58	37	30	25	21	18	16	14	12	11	10
SMART1200XLHG	BP36V15-2U	1	763	427	289	215	139	116	99	85	74	66	59	53	48	44
SMART1200XLHG	BP36V27-2US	1	1,025	582	398	299	194	164	140	121	106	94	84	76	69	64
SMART1200XLHG	BP36V27-2US	2	1,784	1,040	725	551	366	312	268	233	206	183	165	150	137	126
SMART1200XLHG	BP36V27-2US	3	2,502	1,485	1,046	802	540	461	398	348	308	276	250	227	208	192
SMART1200XLHG	BP36V27-2US	4	3,179	1,915	1,361	1,049	712	611	530	464	412	370	335	306	281	260
SMART1200XLHG	BP36V27-2US	5	3,821	2,332	1,668	1,293	883	760	660	580	516	464	421	385	354	328
SMART1200XLHG	BP36V27-2US	6	4,429	2,735	1,968	1,532	1,053	908	790	695	620	559	508	465	428	396
SMART1200XLHG	BP36V27-2US	7	5,005	3,125	2,262	1,766	1,220	1,054	919	810	723	653	594	544	501	465
SMART1200XLHG	BP36V27-2US	8	5,553	3,502	2,548	1,997	1,386	1,199	1,047	924	826	746	679	623	575	534
SMART1200XLHG	BP36V27-2US	9	6,074	3,868	2,828	2,223	1,549	1,342	1,173	1,037	928	839	765	702	648	602
SMART1200XLHG	BP36V27-2US	10	6,570	4,223	3,102	2,446	1,710	1,484	1,299	1,149	1,030	932	850	781	721	671
SMART1200XLHG	BP36V42-3U	1	1,882	1,100	768	585	389	331	285	248	219	196	176	160	146	135
SMART1200XLHG	BP36V42-3U	2	3,354	2,028	1,443	1,115	758	651	564	495	440	395	358	327	300	278
SMART1200XLHG	BP36V42-3U	3	4,663	2,892	2,086	1,626	1,120	966	842	741	661	596	542	496	457	424
SMART1200XLHG	BP36V42-3U	4	5,834	3,699	2,698	2,118	1,473	1,275	1,114	985	881	796	725	665	614	570
SMART1200XLHG	BP36V42-3U	5	6,888	4,453	3,281	2,592	1,817	1,577	1,382	1,224	1,097	993	906	833	770	716
SMART1200XLHG	BP36V42-3U	6	7,842	5,161	3,837	3,048	2,152	1,873	1,644	1,459	1,310	1,188	1,086	999	924	861
SMART1200XLHG	BP36V42-3U	7	8,709	5,824	4,367	3,487	2,478	2,162	1,902	1,690	1,520	1,380	1,263	1,163	1,077	1,004
SMART1200XLHG	BP36V42-3U	8	9,501	6,449	4,873	3,911	2,796	2,444	2,154	1,917	1,726	1,569	1,437	1,325	1,229	1,146
SMART1200XLHG	BP36V42-3U	9	10,227	7,038	5,357	4,320	3,106	2,720	2,401	2,141	1,930	1,756	1,610	1,486	1,379	1,287
SMART1200XLHG	BP36V42-3U	10	10,894	7,594	5,821	4,714	3,408	2,990	2,644	2,360	2,130	1,940	1,780	1,644	1,527	1,426

All runtime values are shown in minutes.