



SMART1500XL Estimated Runtime

UPS	Battery Pack	BP Qty.	Load in Watts													
			50	100	150	200	250	300	400	500	600	700	800	850	900	980
SMART1500XL	Internal batteries	0	233	122	80	58	45	36	26	19	15	12	10	9	8	7
SMART1500XL	BP36V15-2U	1	770	426	288	214	168	137	99	76	59	48	41	37	35	31
SMART1500XL	BP36V27-2US	1	1,034	581	396	296	234	192	139	107	85	69	58	54	50	45
SMART1500XL	BP36V27-2US	2	1,800	1,039	721	547	437	362	267	208	166	137	116	108	100	90
SMART1500XL	BP36V27-2US	3	2,522	1,483	1,041	796	641	534	397	312	251	209	177	165	154	138
SMART1500XL	BP36V27-2US	4	3,205	1,913	1,354	1,042	843	705	528	417	337	281	240	223	209	188
SMART1500XL	BP36V27-2US	5	3,851	2,329	1,660	1,283	1,042	875	658	523	424	355	304	283	265	239
SMART1500XL	BP36V27-2US	6	4,462	2,732	1,959	1,521	1,239	1,043	787	627	511	428	368	343	321	291
SMART1500XL	BP36V27-2US	7	5,042	3,122	2,251	1,754	1,433	1,209	916	732	597	502	432	403	378	343
SMART1500XL	BP36V27-2US	8	5,593	3,499	2,536	1,983	1,624	1,373	1,043	836	683	576	496	463	434	395
SMART1500XL	BP36V27-2US	9	6,116	3,865	2,815	2,208	1,813	1,535	1,170	939	769	649	560	524	491	447
SMART1500XL	BP36V27-2US	10	6,615	4,219	3,088	2,429	1,999	1,695	1,295	1,041	855	722	624	584	548	499
SMART1500XL	BP36V42-3U	1	1,898	1,099	764	580	465	385	284	222	177	147	124	115	107	96
SMART1500XL	BP36V42-3U	2	3,381	2,026	1,436	1,107	896	751	562	445	360	301	257	239	224	202
SMART1500XL	BP36V42-3U	3	4,698	2,889	2,076	1,615	1,317	1,109	839	669	545	458	393	367	344	312
SMART1500XL	BP36V42-3U	4	5,875	3,696	2,686	2,104	1,725	1,459	1,111	891	729	615	530	495	465	422
SMART1500XL	BP36V42-3U	5	6,934	4,450	3,267	2,575	2,121	1,800	1,378	1,109	911	771	667	624	586	533
SMART1500XL	BP36V42-3U	6	7,892	5,156	3,820	3,028	2,505	2,133	1,639	1,325	1,091	926	802	751	706	644
SMART1500XL	BP36V42-3U	7	8,762	5,820	4,348	3,465	2,877	2,456	1,896	1,537	1,269	1,079	936	878	826	754
SMART1500XL	BP36V42-3U	8	9,556	6,444	4,853	3,887	3,238	2,772	2,148	1,745	1,445	1,230	1,070	1,003	945	863
SMART1500XL	BP36V42-3U	9	10,283	7,033	5,336	4,293	3,588	3,079	2,394	1,950	1,618	1,380	1,202	1,128	1,062	972
SMART1500XL	BP36V42-3U	10	10,952	7,588	5,798	4,686	3,928	3,379	2,636	2,153	1,789	1,529	1,332	1,251	1,179	1,079

All runtime values are shown in minutes.