



SMART2200CRMXL Estimated Runtime

UPS	Battery Pack	BP Qty.	Load in Watts													
			100	200	300	400	500	600	800	1,000	1,100	1,200	1,300	1,500	1,700	1,900
SMART2200CRMXL	Included Batteries	0	336	173	112	81	62	50	35	26	23	20	18	15	13	11
SMART2200CRMXL	BP48V24-2U	1	710	381	253	186	145	118	84	64	57	51	46	38	32	28
SMART2200CRMXL	BP48V27-2US	1	895	486	326	241	189	154	111	85	75	67	60	50	43	37
SMART2200CRMXL	BP48V27-2US	2	1,436	799	544	408	323	266	193	149	133	119	108	90	77	67
SMART2200CRMXL	BP48V27-2US	3	1,957	1,106	761	575	458	379	279	217	193	174	158	132	114	99
SMART2200CRMXL	BP48V27-2US	4	2,457	1,407	976	741	594	493	365	285	255	230	209	176	151	132
SMART2200CRMXL	BP48V27-2US	5	2,937	1,701	1,187	906	728	607	451	354	317	287	261	221	190	166
SMART2200CRMXL	BP48V27-2US	6	3,399	1,989	1,395	1,069	862	720	537	423	380	344	313	266	229	201
SMART2200CRMXL	BP48V27-2US	7	3,844	2,271	1,601	1,230	995	833	623	493	443	401	366	311	269	236
SMART2200CRMXL	BP48V27-2US	8	4,272	2,546	1,803	1,389	1,126	944	709	562	505	458	419	356	309	272
SMART2200CRMXL	BP48V27-2US	9	4,685	2,815	2,002	1,547	1,257	1,055	795	631	568	516	472	402	349	307
SMART2200CRMXL	BP48V27-2US	10	5,083	3,079	2,198	1,703	1,386	1,165	880	700	631	573	524	447	389	343
SMART2200CRMXL	BP48V48RT-4U*	1	1,222	674	457	341	269	221	160	123	109	98	88	74	63	55
SMART2200CRMXL	BP48V48RT-4U*	2	2,058	1,167	804	608	486	402	296	230	205	185	168	141	121	105
SMART2200CRMXL	BP48V48RT-4U*	3	2,843	1,643	1,145	873	702	584	434	340	305	275	251	212	182	160
SMART2200CRMXL	BP48V48RT-4U*	4	3,579	2,103	1,478	1,133	915	765	572	451	405	367	335	284	245	215
SMART2200CRMXL	BP48V48RT-4U*	5	4,272	2,546	1,803	1,389	1,126	944	709	562	505	458	419	356	309	272
SMART2200CRMXL	BP48V48RT-4U*	6	4,926	2,974	2,120	1,641	1,334	1,121	846	672	606	550	503	429	373	329
SMART2200CRMXL	BP48V48RT-4U*	7	5,542	3,387	2,429	1,887	1,539	1,296	981	782	705	642	588	502	437	386
SMART2200CRMXL	BP48V48RT-4U*	8	6,125	3,787	2,730	2,129	1,740	1,469	1,115	891	805	733	672	575	501	443
SMART2200CRMXL	BP48V48RT-4U*	9	6,677	4,173	3,025	2,366	1,939	1,640	1,248	1,000	903	823	755	647	565	500
SMART2200CRMXL	BP48V48RT-4U*	10	7,201	4,546	3,312	2,599	2,134	1,808	1,380	1,107	1,001	913	839	720	629	557

All runtime values are shown in minutes. * BP48V60RT3U can be substituted for BP48V48RT-4U with the same runtime performance.