



## SM2200RMXL2UP Estimated Runtime

UPS	Battery Configuration		Connected Equipment Load in Watts													
			100	200	300	400	500	600	700	800	1,000	1,200	1,400	1,600	1,800	1,920
SM2200RMXL2UP	Internal batteries		150	75	48	35	27	21	18	15	11	8.8	7.0	5.8	4.9	4.5
SM2200RMXL2UP	BP48V24-2U	1	515	272	179	131	102	82	68	58	44	34	28	23	20	18
SM2200RMXL2UP	BP48V27-2US	1	699	375	250	184	143	117	97	83	63	49	40	33	29	26
SM2200RMXL2UP	BP48V27-2US	2	1,239	685	465	347	274	225	190	163	126	99	81	68	58	53
SM2200RMXL2UP	BP48V27-2US	3	1,759	990	680	512	408	337	285	247	191	152	125	105	90	83
SM2200RMXL2UP	BP48V27-2US	4	2,259	1,290	893	677	542	449	382	332	258	206	170	144	124	115
SM2200RMXL2UP	BP48V27-2US	5	2,739	1,583	1,103	840	675	562	479	417	327	262	217	184	159	147
SM2200RMXL2UP	BP48V27-2US	6	3,202	1,869	1,310	1,002	808	674	576	502	395	317	264	224	195	180
SM2200RMXL2UP	BP48V27-2US	7	3,647	2,150	1,514	1,162	939	785	673	587	463	373	311	265	230	213
SM2200RMXL2UP	BP48V27-2US	8	4,076	2,424	1,714	1,320	1,070	896	769	672	532	430	359	306	267	247
SM2200RMXL2UP	BP48V27-2US	9	4,489	2,692	1,912	1,477	1,199	1,006	865	757	600	486	406	348	303	281
SM2200RMXL2UP	BP48V27-2US	10	4,888	2,955	2,107	1,631	1,327	1,115	960	841	668	542	454	389	339	315
SM2200RMXL2UP	BP48V60RT3UTAA	1	1,025	562	378	281	221	181	152	131	100	79	64	54	46	42
SM2200RMXL2UP	BP48V60RT3UTAA	2	1,860	1,051	723	545	435	359	305	264	205	163	134	113	97	89
SM2200RMXL2UP	BP48V60RT3UTAA	3	2,645	1,525	1,061	808	649	539	460	400	313	250	207	176	152	140
SM2200RMXL2UP	BP48V60RT3UTAA	4	3,382	1,982	1,392	1,066	860	719	615	536	422	340	283	241	209	193
SM2200RMXL2UP	BP48V60RT3UTAA	5	4,076	2,424	1,714	1,320	1,070	896	769	672	532	430	359	306	267	247
SM2200RMXL2UP	BP48V60RT3UTAA	6	4,730	2,851	2,030	1,570	1,276	1,072	922	808	641	520	435	372	325	301
SM2200RMXL2UP	BP48V60RT3UTAA	7	5,348	3,262	2,337	1,814	1,479	1,245	1,073	942	749	609	511	439	383	356
SM2200RMXL2UP	BP48V60RT3UTAA	8	5,933	3,661	2,637	2,055	1,679	1,417	1,223	1,075	857	699	587	505	442	410
SM2200RMXL2UP	BP48V60RT3UTAA	9	6,486	4,046	2,930	2,290	1,876	1,586	1,371	1,206	965	787	663	571	500	465
SM2200RMXL2UP	BP48V60RT3UTAA	10	7,011	4,418	3,216	2,522	2,070	1,753	1,518	1,337	1,071	876	739	637	558	520

All runtime values are shown in minutes.