



SMX2200XLRT2UN Estimated Runtime

UPS	Battery Configuration	CONNECTED EQUIPMENT LOAD IN WATTS													
		20	50	80	100	150	200	400	600	800	1,000	1,200	1,400	1,500	1,920
SMX2200XLRT2UN	INCLUDED BATTERIES	421	255	179	148	101	75	35	21	15	11	9.0	7.4	6.8	5.0

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			20	50	80	100	150	200	400	600	800	1,000	1,200	1,400	1,500	1,600
SMX2200XLRT2UN	BP48V24-2U	1	1,320	837	605	509	359	274	133	84	60	45	35	29	26	24
SMX2200XLRT2UN	BP48V27-2US	1	1,750	1,122	818	690	491	378	187	119	85	65	51	42	38	35
SMX2200XLRT2UN	BP48V27-2US	2	2,959	1,944	1,440	1,224	885	689	353	230	167	129	102	84	77	71
SMX2200XLRT2UN	BP48V27-2US	3	4,058	2,717	2,034	1,739	1,270	996	521	344	253	196	157	129	119	109
SMX2200XLRT2UN	BP48V27-2US	4	5,061	3,443	2,601	2,234	1,645	1,297	688	459	339	265	213	176	162	150
SMX2200XLRT2UN	BP48V27-2US	5	5,979	4,127	3,144	2,710	2,009	1,591	854	574	427	335	270	224	206	191
SMX2200XLRT2UN	BP48V27-2US	6	6,824	4,773	3,663	3,168	2,363	1,879	1,018	688	514	405	327	273	251	233
SMX2200XLRT2UN	BP48V27-2US	7	7,603	5,383	4,160	3,610	2,707	2,160	1,180	801	601	475	385	322	297	275
SMX2200XLRT2UN	BP48V27-2US	8	8,324	5,961	4,636	4,035	3,042	2,436	1,341	914	688	545	443	371	342	318
SMX2200XLRT2UN	BP48V27-2US	9	8,993	6,508	5,092	4,445	3,367	2,705	1,499	1,026	774	615	500	420	388	360
SMX2200XLRT2UN	BP48V27-2US	10	9,615	7,027	5,531	4,841	3,684	2,969	1,656	1,137	860	685	558	469	434	403
SMX2200XLRT2UN	BP48V60RT-3U	1	2,490	1,621	1,194	1,013	729	565	286	185	134	103	81	66	61	56
SMX2200XLRT2UN	BP48V60RT-3U	2	4,266	2,865	2,149	1,839	1,346	1,056	554	367	270	210	168	139	127	117
SMX2200XLRT2UN	BP48V60RT-3U	3	5,802	3,994	3,037	2,616	1,937	1,533	821	551	409	321	258	215	198	183
SMX2200XLRT2UN	BP48V60RT-3U	4	7,143	5,021	3,864	3,347	2,502	1,992	1,083	733	549	433	350	292	270	250
SMX2200XLRT2UN	BP48V60RT-3U	5	8,324	5,961	4,636	4,035	3,042	2,436	1,341	914	688	545	443	371	342	318
SMX2200XLRT2UN	BP48V60RT-3U	6	9,371	6,823	5,358	4,684	3,558	2,864	1,594	1,093	826	657	535	449	415	386
SMX2200XLRT2UN	BP48V60RT-3U	7	10,307	7,617	6,034	5,297	4,053	3,278	1,842	1,269	962	768	627	528	489	454
SMX2200XLRT2UN	BP48V60RT-3U	8	11,148	8,350	6,669	5,878	4,528	3,678	2,085	1,444	1,098	878	719	606	562	523
SMX2200XLRT2UN	BP48V60RT-3U	9	11,908	9,030	7,267	6,428	4,983	4,064	2,324	1,616	1,232	988	810	684	634	591
SMX2200XLRT2UN	BP48V60RT-3U	10	12,599	9,662	7,831	6,950	5,420	4,438	2,558	1,786	1,365	1,097	901	762	707	659

All runtime values are shown in minutes.