



SMART2000RMXL2U Estimated Runtime

UPS	Battery Configuration	CONNECTED EQUIPMENT LOAD IN WATTS													
		100	200	400	600	800	1,000	1,200	1,300	1,400	1,500	1,600	1,700	1,800	1,920
SMART2000RMXL2U	Internal Batteries Only	150	75	35	21	15	11	9	8	7	6	6	5	5	4

Maximum load supported WITHOUT external battery packs is 1920 watts. All runtime values are shown in minutes.

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			100	200	400	600	700	800	900	1,000	1,100	1,200	1,300	1,400	1,500	1,600
SMART2000RMXL2U	BP48V24-2U	1	515	272	131	82	68	58	50	44	39	34	31	28	25	23
SMART2000RMXL2U	BP48V27-2US	1	699	375	184	117	97	83	72	63	56	49	44	40	36	33
SMART2000RMXL2U	BP48V27-2US	2	1,239	685	347	225	190	163	143	126	111	99	89	81	74	68
SMART2000RMXL2U	BP48V27-2US	3	1,759	990	512	337	285	247	216	191	169	152	137	125	114	105
SMART2000RMXL2U	BP48V27-2US	4	2,259	1,290	677	449	382	332	292	258	230	206	187	170	156	144
SMART2000RMXL2U	BP48V27-2US	5	2,739	1,583	840	562	479	417	368	327	291	262	237	217	199	184
SMART2000RMXL2U	BP48V27-2US	6	3,202	1,869	1,002	674	576	502	444	395	352	317	288	264	243	224
SMART2000RMXL2U	BP48V27-2US	7	3,647	2,150	1,162	785	673	587	520	463	414	373	340	311	287	265
SMART2000RMXL2U	BP48V27-2US	8	4,076	2,424	1,320	896	769	672	596	532	476	430	391	359	331	306
SMART2000RMXL2U	BP48V27-2US	9	4,489	2,692	1,477	1,006	865	757	672	600	537	486	443	406	375	348
SMART2000RMXL2U	BP48V27-2US	10	4,888	2,955	1,631	1,115	960	841	747	668	599	542	494	454	419	389
SMART2000RMXL2U	BP48V60RT-3U	1	1,025	562	281	181	152	131	114	100	88	79	71	64	58	54
SMART2000RMXL2U	BP48V60RT-3U	2	1,860	1,051	545	359	305	264	231	205	181	163	147	134	123	113
SMART2000RMXL2U	BP48V60RT-3U	3	2,645	1,525	808	539	460	400	353	313	279	250	227	207	190	176
SMART2000RMXL2U	BP48V60RT-3U	4	3,382	1,982	1,066	719	615	536	474	422	377	340	309	283	260	241
SMART2000RMXL2U	BP48V60RT-3U	5	4,076	2,424	1,320	896	769	672	596	532	476	430	391	359	331	306
SMART2000RMXL2U	BP48V60RT-3U	6	4,730	2,851	1,570	1,072	922	808	717	641	574	520	474	435	401	372
SMART2000RMXL2U	BP48V60RT-3U	7	5,348	3,262	1,814	1,245	1,073	942	838	749	673	609	556	511	472	439
SMART2000RMXL2U	BP48V60RT-3U	8	5,933	3,661	2,055	1,417	1,223	1,075	957	857	770	699	638	587	543	505
SMART2000RMXL2U	BP48V60RT-3U	9	6,486	4,046	2,290	1,586	1,371	1,206	1,076	965	868	787	720	663	614	571
SMART2000RMXL2U	BP48V60RT-3U	10	7,011	4,418	2,522	1,753	1,518	1,337	1,193	1,071	964	876	802	739	684	637

Maximum load supported WITH external battery packs is 1600 watts. All runtime values are shown in minutes.