



SU2200RTXLCDN Estimated Runtime

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			100	200	300	400	500	600	700	800	900	1,000	1,200	1,400	1,600	1,800
SU2200RTXLCDN	Internal batteries	n/a	141	70	45	32	25	20	16	14	12	10	7.8	6.1	4.9	4.0
SU2200RTXLCDN	BP48V24-2U	1	486	258	170	124	96	78	65	55	48	42	33	27	23	19
SU2200RTXLCDN	BP48V27-2US	1	660	356	237	174	136	110	92	79	68	60	48	39	33	28
SU2200RTXLCDN	BP48V27-2US	2	1,174	651	442	330	261	214	180	155	135	119	96	79	67	58
SU2200RTXLCDN	BP48V27-2US	3	1,669	942	647	488	388	320	271	235	206	182	147	122	104	90
SU2200RTXLCDN	BP48V27-2US	4	2,146	1,228	850	645	516	428	364	316	278	246	200	167	143	124
SU2200RTXLCDN	BP48V27-2US	5	2,606	1,509	1,051	801	644	536	457	397	350	311	254	213	182	159
SU2200RTXLCDN	BP48V27-2US	6	3,050	1,783	1,250	956	771	643	550	479	423	377	308	259	222	194
SU2200RTXLCDN	BP48V27-2US	7	3,477	2,052	1,445	1,109	897	750	642	560	496	443	362	305	263	230
SU2200RTXLCDN	BP48V27-2US	8	3,890	2,315	1,638	1,261	1,022	856	734	642	569	508	417	352	303	266
SU2200RTXLCDN	BP48V27-2US	9	4,288	2,573	1,828	1,411	1,145	961	826	723	641	574	472	399	344	302
SU2200RTXLCDN	BP48V27-2US	10	4,673	2,826	2,015	1,560	1,268	1,066	917	804	714	639	526	446	385	338
SU2200RTXLCDN	BP48V60RT-3U	1	970	533	359	267	210	172	144	124	108	95	76	63	53	46
SU2200RTXLCDN	BP48V60RT-3U	2	1,766	1,000	688	519	414	342	290	251	220	195	157	131	112	97
SU2200RTXLCDN	BP48V60RT-3U	3	2,516	1,453	1,011	770	618	514	438	381	336	298	243	203	174	152
SU2200RTXLCDN	BP48V60RT-3U	4	3,223	1,892	1,328	1,018	821	686	587	511	452	403	330	277	238	208
SU2200RTXLCDN	BP48V60RT-3U	5	3,890	2,315	1,638	1,261	1,022	856	734	642	569	508	417	352	303	266
SU2200RTXLCDN	BP48V60RT-3U	6	4,521	2,725	1,940	1,501	1,219	1,024	881	771	685	613	504	427	369	324
SU2200RTXLCDN	BP48V60RT-3U	7	5,118	3,122	2,236	1,736	1,414	1,191	1,026	900	800	717	592	502	434	382
SU2200RTXLCDN	BP48V60RT-3U	8	5,684	3,506	2,525	1,967	1,607	1,355	1,170	1,027	915	821	679	577	500	440
SU2200RTXLCDN	BP48V60RT-3U	9	6,222	3,878	2,807	2,193	1,796	1,518	1,312	1,154	1,029	924	765	651	565	498
SU2200RTXLCDN	BP48V60RT-3U	10	6,733	4,238	3,082	2,416	1,983	1,678	1,453	1,279	1,142	1,026	852	726	631	557

All runtime values are shown in minutes.