



SMART5000XFMRL Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Watts													
			500	750	1,000	1,250	1,500	1,750	2,000	2,250	2,500	2,750	3,000	3,250	3,500	3,750
SMART5000XFMRL	INTERNAL BATTERIES	0	98	61	44	33	27	22	18	16	14	12	11	10	9.2	8.5
SMART5000XFMRL	BP48V27-2US	1	224	143	105	81	66	54	46	39	34	30	27	24	22	20
SMART5000XFMRL	BP48V27-2US	2	354	230	171	132	108	89	76	65	57	51	45	41	37	34
SMART5000XFMRL	BP48V27-2US	3	484	319	239	185	152	127	109	93	82	73	65	59	53	49
SMART5000XFMRL	BP48V27-2US	4	615	408	307	240	198	165	142	122	108	95	86	77	70	64
SMART5000XFMRL	BP48V27-2US	5	745	497	376	295	244	204	176	152	134	119	107	97	88	81
SMART5000XFMRL	BP48V27-2US	6	874	587	445	350	290	244	210	182	161	143	129	117	106	98
SMART5000XFMRL	BP48V27-2US	7	1,001	675	514	405	337	284	245	212	188	167	151	137	125	115
SMART5000XFMRL	BP48V27-2US	8	1,128	764	583	461	384	324	280	243	215	192	173	157	144	132
SMART5000XFMRL	BP48V27-2US	9	1,254	852	652	516	431	364	316	274	243	217	196	178	163	150
SMART5000XFMRL	BP48V27-2US	10	1,378	940	721	572	478	404	351	305	271	242	219	199	182	168
SMART5000XFMRL	BP48V60RT-3U	1	302	195	144	111	91	75	64	55	48	42	38	34	31	28
SMART5000XFMRL	BP48V60RT-3U	2	511	337	252	196	161	134	115	99	87	77	69	62	57	52
SMART5000XFMRL	BP48V60RT-3U	3	719	480	362	284	235	196	169	146	129	114	103	93	85	77
SMART5000XFMRL	BP48V60RT-3U	4	925	622	473	372	309	260	224	194	172	153	137	125	114	104
SMART5000XFMRL	BP48V60RT-3U	5	1,128	764	583	461	384	324	280	243	215	192	173	157	144	132
SMART5000XFMRL	BP48V60RT-3U	6	1,329	905	693	550	459	388	337	292	260	232	209	190	174	160
SMART5000XFMRL	BP48V60RT-3U	7	1,526	1,044	803	638	534	453	393	342	304	272	246	224	205	189
SMART5000XFMRL	BP48V60RT-3U	8	1,721	1,182	911	726	609	517	450	392	349	313	283	258	236	218
SMART5000XFMRL	BP48V60RT-3U	9	1,913	1,319	1,019	814	684	581	507	442	394	354	320	292	268	247
SMART5000XFMRL	BP48V60RT-3U	10	2,102	1,454	1,126	901	759	645	563	491	439	394	357	326	300	277

*Remove all internal battery modules before connecting any external battery packs. All runtime values are shown in minutes.