



## SMX5000XLRT3U Estimated Runtime

UPS	Battery Pack	BP Qty.	Load in Watts													
			300	600	900	1,200	1,500	1,800	2,100	2,400	2,700	3,000	3,200	3,400	3,600	3,750
SMX5000XLRT3U	Included Batteries	0	167	80	50	35	27	21	17	15	13	11	10	9.6	8.9	8.5
SMX5000XLRT3U	BP48V24-2U	1	300	149	95	68	52	42	34	29	24	21	19	18	17	16
SMX5000XLRT3U	BP48V27-2US	1	368	185	119	85	66	53	43	36	31	27	25	23	21	20
SMX5000XLRT3U	BP48V27-2US	2	571	295	192	139	108	87	72	60	52	45	42	38	36	34
SMX5000XLRT3U	BP48V27-2US	3	773	405	267	196	152	124	102	86	74	65	60	55	51	49
SMX5000XLRT3U	BP48V27-2US	4	973	516	343	253	198	161	134	113	98	86	79	73	68	64
SMX5000XLRT3U	BP48V27-2US	5	1,170	627	419	310	244	199	166	141	122	107	99	91	85	81
SMX5000XLRT3U	BP48V27-2US	6	1,364	737	496	368	290	238	198	169	146	129	119	110	103	98
SMX5000XLRT3U	BP48V27-2US	7	1,555	847	572	427	337	277	231	197	171	151	139	129	121	115
SMX5000XLRT3U	BP48V27-2US	8	1,744	955	648	485	384	316	265	226	196	173	160	149	139	132
SMX5000XLRT3U	BP48V27-2US	9	1,930	1,063	724	543	431	355	298	255	222	196	181	169	157	150
SMX5000XLRT3U	BP48V27-2US	10	2,114	1,170	799	601	478	395	332	284	247	219	202	188	176	168
SMX5000XLRT3U	BP48V60RT-3U	1	490	251	162	118	91	73	60	50	43	38	35	32	30	28
SMX5000XLRT3U	BP48V60RT-3U	2	813	427	282	207	161	131	108	92	79	69	63	59	55	52
SMX5000XLRT3U	BP48V60RT-3U	3	1,130	605	404	299	235	192	159	135	117	103	95	88	82	77
SMX5000XLRT3U	BP48V60RT-3U	4	1,441	781	526	392	309	254	212	180	156	137	127	118	110	104
SMX5000XLRT3U	BP48V60RT-3U	5	1,744	955	648	485	384	316	265	226	196	173	160	149	139	132
SMX5000XLRT3U	BP48V60RT-3U	6	2,041	1,128	769	578	459	379	318	272	237	209	194	180	168	160
SMX5000XLRT3U	BP48V60RT-3U	7	2,330	1,298	889	670	534	442	372	319	278	246	228	212	199	189
SMX5000XLRT3U	BP48V60RT-3U	8	2,613	1,466	1,008	762	609	505	426	366	320	283	263	245	229	218
SMX5000XLRT3U	BP48V60RT-3U	9	2,890	1,632	1,127	854	684	568	480	413	361	320	297	277	259	247
SMX5000XLRT3U	BP48V60RT-3U	10	3,161	1,796	1,244	945	759	631	533	459	402	357	332	310	290	277

All runtime values are shown in minutes.