






REV	ECO #	DESCRIPTION	DR	DATE
01	0302309	ENGINEERING RELEASE	R.W.	APR 07 2025



EMAGECC2C2C2L HDX MANAGED

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	HARDWIRED, CLEARANCE HOLE 1.734" FOR 1.25" CONDUIT	(48) IEC C13 GRIP	UL / cUL LISTED CE CERTIFIED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
69.4" (1764mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V / 346-415 ~ WYE, 3W + N + PE 48-64A 50/60Hz 60-80A PANEL BREAKER	200-240V ~ 10A PER C13, 16A PER C19 16A MAX PER SECTION 48-64A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): EMAGECC2C2C2L	REVISION: 01	EATON
DESCRIPTION: EPDU HDX MA HRDWIRED WYE 48xC13		SIZE: D		
ORIGINATED BY: RUTUJA W	DEC-23-2024	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE: Release	SCALE: 0.100
MODIFIED BY: R. Wani	APR-07-2025	ECO: CO-0302309	SHEET: 1 OF 1	

EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT, INCLUDING THE INFORMATION CONTAINED HEREIN, IS CONFIDENTIAL AND IS NOT TO BE DISCLOSED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF EATON. THE INFORMATION CONTAINED HEREIN IS THE PROPERTY OF EATON CORPORATION AND IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT THE WRITTEN CONSENT OF EATON. IN THE USE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2025 Eaton Corporation. All Rights Reserved.