





REV	ECO #	DESCRIPTION	DR	DATE
01	CO-0318408	ENGINEERING RELEASE	R.W.	FEB 24 2025



**EMAGECC3C3C3L
HDX MANAGED**

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	HARDWIRED, CLEARANCE HOLE 1.734" FOR 1.25" CONDUIT	(12) C39 - COMBINATION C13 + C19 (24) IEC C13 GRIP	UL / cUL LISTED CE
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
69.4" (1764mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V /346-415V ~ WYE, 3W + N + PE 48-64A 50/60Hz 60-80A PANEL BREAKER	200-240V ~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 48-64A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): EMAGECC3C3C3L	REVISION: 01	EATON
DESCRIPTION: EPDU HDX MA HW 415V 48-64A, 24xC13:12xC39		SIZE: D		
ORIGINATED BY: RUTUJA W	DEC 24 2024	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING	STATE: Release	SCALE: 0.35
MODIFIED BY: R. Wani	FEB 24 2025	INTERPRET DIM AND TOL PER ASME Y14.5-2018	ECO: CO-0318408	SHEET: 1 OF 1
<small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT IS THE PROPERTY OF EATON CORPORATION AND IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE WRITTEN CONSENT OF EATON CORPORATION. ANY UNAUTHORIZED REPRODUCTION OR USE OF THIS DOCUMENT IS STRICTLY PROHIBITED. EATON CORPORATION SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING CONSEQUENTIAL DAMAGES, ARISING FROM THE USE OF THIS DOCUMENT. THE USER SHALL OBTAIN THE STATUS OF THIS DOCUMENT FROM Eaton Corporation. All Rights Reserved.</small>				