


REV	ECO #	DESCRIPTION	DR	DATE
01	0302309	ENGINEERING RELEASE	R.W.	APR 04 2025



**EMAGFFA4A4A4L  
HDX MANAGED**

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	IEC 60309 560P6W PLUG 6FT 6AWG, 5C POWERCORD	(24) IEC C19 GRIP (24) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
76.0" (1930mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V / 346-415 ~ WYE, 3W + N + PE 48A 50/60Hz	200-240V ~ 10A PER C13, 16A PER C19 16A MAX PER SECTION 48A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): EMAGFFA4A4A4L	REVISION: 01	<b>EATON</b>
DESCRIPTION: EPDU HDX MA 560P6W WYE 24x13, 24x19		SIZE: D		
ORIGINATED BY: RUTUJA W	DEC-23-2024	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE: Release	SCALE: 0.33
MODIFIED BY: R. Wanl	APR-04-2025	ECO: CO-0302309	SHEET: 1 OF 1	

EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT IS THE PROPERTY OF EATON AND IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT THE WRITTEN PERMISSION OF EATON. ANY UNAUTHORIZED REPRODUCTION OR USE OF THIS DOCUMENT IS STRICTLY PROHIBITED. IN THE USE OF CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE ENTIRETY OF THIS DOCUMENT. © 2025 Eaton Corporation. All Rights Reserved.