



EMAGFFA5A2A5A2L HDX MANAGED

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	IEC 60309 560P6W PLUG 6FT 6AWG, 5C POWERCORD	(12) C39 - COMBINATION C13 + C19 (42) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
76.0" (1930mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V / 346-415 ~ WYE, 3W + N + PE 48A 50/60Hz	200-240V ~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 48A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): EMAGFFA5A2A5A2L	REVISION: 01	EATON
DESCRIPTION: EPDU HDX MA 560P6W WYE 42xC13 12xC39		SIZE: D		
ORIGINATED BY: RUTUJA W	DEC 23 2024	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE: Release	SCALE: 0.300
MODIFIED BY: R. Wani	FEB 24 2025		ECO: CO-0318408	SHEET: 1 OF 1
<small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT, INCLUDING THE INFORMATION THEREON, IS CONFIDENTIAL AND NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF EATON CORPORATION. ANY UNAUTHORIZED REPRODUCTION OR USE OF THIS DOCUMENT OR THE INFORMATION THEREON MAY BE SUBJECT TO LEGAL ACTION. THIS DOCUMENT IS THE PROPERTY OF EATON CORPORATION AND IS TO BE KEPT IN CONFIDENTIALITY. ANY UNAUTHORIZED REPRODUCTION OR USE OF THIS DOCUMENT OR THE INFORMATION THEREON MAY BE SUBJECT TO LEGAL ACTION. THIS DOCUMENT IS THE PROPERTY OF EATON CORPORATION AND IS TO BE KEPT IN CONFIDENTIALITY. ANY UNAUTHORIZED REPRODUCTION OR USE OF THIS DOCUMENT OR THE INFORMATION THEREON MAY BE SUBJECT TO LEGAL ACTION.</small>				