



REV	ECO #	DESCRIPTION	DR	DATE
01	0302309	ENGINEERING RELEASE	R.W.	APR 07 2025



**EMAGFFA5A5A5L
HDX MANAGED**

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	IEC 60309 560P6W PLUG 6FT 6AWG, 5C POWERCORD	(24) C39 - COMBINATION C13 + C19 (24) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
76.0" (1930mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V / 346-415 ~ WYE, 3W + N + PE 48A 50/60Hz	200-240V ~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 48A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): EMAGFFA5A5A5L	REVISION: 01	EATON
DESCRIPTION: EPDU HDX MA 560P6W WYE 24xC13, 24xC39		SIZE: D		
ORIGINATED BY: RUTUJA W	DEC-23-2024	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE: Release	SCALE: 0.100
MODIFIED BY: R. Wanl	APR-07-2025	ECO: CO-0302309		SHEET: 1 OF 1
<small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT IS THE PROPERTY OF EATON AND IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE WRITTEN CONSENT OF EATON. IN THE USE OF CONFIDENTIAL INFORMATION, THIS NOTICE SHALL GOVERN THE ENTIRETY OF THIS DOCUMENT. © 2025 Eaton Corporation. All Rights Reserved.</small>				