



**EMAGFFC2C2C2L
HDX MANAGED**

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	IEC 60309 560P6W PLUG 6FT 6AWG, 5C POWERCORD	(48) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
69.4" (1764mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V / 346-415V ~ WYE, 3W + N + PE 48A 50/60Hz	200-240V ~ 10A PER C13 16A MAX PER SECTION 48A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): EMAGFFC2C2C2L	REVISION: 01	EATON
DESCRIPTION: EPDU HDX MA 560P6W WYE 48x13		SIZE: D		
ORIGINATED BY: RUTUJA W	DEC-24-2024	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING	STATE: Release	SCALE: 0.100
MODIFIED BY: R. Wanl	APR-07-2025	INTERPRET DIM AND TOL PER ASME Y14.5-2018	ECO: CO-0302309	SHEET: 1 OF 1
<small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT, INCLUDING THE INFORMATION THEREON, IS CONFIDENTIAL AND NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF EATON. ANY UNAUTHORIZED REPRODUCTION OR USE OF THIS DOCUMENT OR THE INFORMATION THEREON IS STRICTLY PROHIBITED. IN THE USE OF CONFIDENTIAL INFORMATION, THIS NOTICE SHALL GOVERN THE STATUS OF THE DOCUMENT. © 2025 Eaton Corporation. All Rights Reserved.</small>				