


REV	ECO #	DESCRIPTION	DR	DATE
01	CO-0318408	ENGINEERING RELEASE	R.W.	FEB 24 2025



**EMAGFFC3C3C3L
HDX MANAGED**

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	IEC 60309 560P6W PLUG 6FT 6AWG, 5C POWERCORD	(12) C39 - COMBINATION C13 + C19 (24) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
69.4" (1764mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V /346-415 ~ WYE, 3W + N + PE 48A 50/60Hz	200-240V ~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 48A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): EMAGFFC3C3C3L	REVISION: 01	EATON
DESCRIPTION: EPDU HDX MA 560P6W 6FT UL, 24x13 12x13		SIZE: D		
ORIGINATED BY: RUTUJA W	DEC-24-2024	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING	STATE: Release	SCALE: 0.35
MODIFIED BY: R. Wani	FEB-24-2025	INTERPRET DIM AND TOL PER ASME Y14.5-2018	ECO: CO-0318408	SHEET: 1 OF 1
<small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT IS THE PROPERTY OF EATON AND IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE WRITTEN CONSENT OF EATON. THE INFORMATION CONTAINED HEREIN IS CONFIDENTIAL AND PROPRIETARY. ANY UNAUTHORIZED DISCLOSURE OR USE OF THIS INFORMATION IS STRICTLY PROHIBITED. EATON ACCEPTS NO LIABILITY FOR ANY DAMAGE, INCLUDING CONSEQUENTIAL DAMAGES, ARISING FROM THE USE OF THIS DOCUMENT. THIS NOTICE SHALL GOVERN THE ENTIRETY OF THIS DOCUMENT. © 2025 Eaton Corporation. All Rights Reserved.</small>				