



REV	ECO #	DESCRIPTION	DR	DATE
01	CO-0318408	ENGINEERING RELEASE	R.W.	FEB 24 2025



## EMAGFFC4C4C4L HDX MANAGED

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	IEC 60309 560P6W PLUG 6FT 6AWG, 5C POWERCORD	(24) C39 - COMBINATION C13 + C19	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
76.0" (1764mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V / 346-415 ~ WYE, 3W + N + PE 48A 50/60Hz	200-240V ~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 48A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

<b>METRIC</b>	THIRD ANGLE PROJECTION	NAME (PART NUMBER): <b>EMAGFFC4C4C4L</b>	REVISION: <b>01</b>	<b>EATON</b>
DESCRIPTION: EPDU HDX MA 560P6W WYE 24x39		SIZE: D		
ORIGINATED BY: RUTUJA W	DEC-24-2024	SEE NOTES FOR TOLERANCES. DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATUS: RELEASED	SCALE: 0.35
MODIFIED BY: RUTUJA W	FEB-24-2025	ECO: CO-0318408	SHEET: 1 OF 1	

EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT, INCLUDING DRAWINGS AND INFORMATION CONTAINED THEREIN, IS CONFIDENTIAL AND IS THE PROPERTY OF EATON CORPORATION AND IS SUBJECT TO EATON'S PATENT AND TRADE SECRET RIGHTS. IT IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE WRITTEN CONSENT OF EATON. IN THE CASE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2025 Eaton Corporation. All Rights Reserved.