



EMAGKEA5A5A5A5L HDX MANAGED

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	HARDWIRED, CLEARANCE HOLE 1.734" FOR 1.25" CONDUIT	(24) C39 - COMBINATION C13 + C19 (24) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
76.0" (1930mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V ~ DELTA, 3W + PE 48-100A 50/60Hz 60-125A PANEL BREAKER	200-240V ~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 48-100A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): EMAGKEA5A5A5A5L	REVISION: 01	EATON
DESCRIPTION: EPDU HDX MA HRDWIRED DEL 24xC13, 24xC39		SIZE: D		
ORIGINATED BY: SATYAN, S	APR 03 2025	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE: Release	SCALE: 0.100
MODIFIED BY: S. Sangamesh	APR 03 2025	ECO: CO-0302309	SHEET: 1 OF 1	
<small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT IS THE PROPERTY OF EATON AND IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE WRITTEN CONSENT OF EATON. IN THE USE OF CONFIDENTIAL INFORMATION, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2025 Eaton Corporation. All Rights Reserved.</small>				