





REV	ECO #	DESCRIPTION	DR	DATE
03	CO-0318408	ENGINEERING RELEASE	S.S	FEB 26 2025



EMAGKEA5A2A5A2L HDX MANAGED

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	HARDWIRED, CLEARANCE HOLE 1.734" FOR 1.25" CONDUIT	(12) C39 - COMBINATION C13 + C19 (42) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
76.0" (1930mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V ~ DELTA, 3W + PE 48-100A 50/60Hz 60-125A PANEL BREAKER	200-240V ~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 48-100A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER):	REVISION: 01	EATON
DESCRIPTION: EPDU HDX MA HRDWIRED DEL 42xC13, 12xC39		EMAGKEA5A2A5A2L		SIZE: D
ORIGINATED BY: SATYAN. S	FEB 26 2025	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE: Release	SCALE: 0.35
MODIFIED BY: S. Sengameeh	FEB 26 2025		ECO: CO-0318408	SHEET: 1 of 1
EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT IS THE PROPERTY OF EATON CORPORATION AND IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT THE PRIOR WRITTEN CONSENT OF EATON. IN THE USE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2015 Eaton Corporation. All Rights Reserved.				