





REV	ECO #	DESCRIPTION	DR	DATE
01	CO-0302309	ENGINEERING RELEASE	S.S	APR 08 2025



**EMAGKEC2C2C2L
HDX MANAGED**

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	HARDWIRED, CLEARANCE HOLE 1.734" FOR 1.25" CONDUIT	(48) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
69.4" (1764mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V ~ DELTA, 3W + PE 48-100A 50/60Hz 60-125A PANEL BREAKER	200-240V ~ 10A PER C13 16A MAX PER SECTION 48-100A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): EMAGKEC2C2C2L	REVISION: 01	EATON
DESCRIPTION: EPDU HDX MA HRDWIRED DELTA 48xC13		SIZE: D		
ORIGINATED BY: SATYAN. S	APR 08 2025	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE: Release	SCALE: 0.100
MODIFIED BY: S. Sangamesh	APR 08 2025	ECO: CO-0302309	SHEET: 1 OF 1	

EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT, INCLUDING THE INFORMATION CONTAINED HEREIN, IS CONFIDENTIAL AND NOT TO BE REPRODUCED, COPIED, OR DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN CONSENT OF EATON. ANY UNAUTHORIZED REPRODUCTION OR DISCLOSURE OF THIS DOCUMENT OR THE INFORMATION CONTAINED HEREIN IS STRICTLY PROHIBITED. IN THE USE OF CONFIDENTIAL INFORMATION, THIS NOTICE SHALL GOVERN THE CONDUCT OF THE USER. © 2025 Eaton Corporation. All Rights Reserved.