





REV	ECO #	DESCRIPTION	DR	DATE
01	CO-0318408	ENGINEERING CONCEPT	S.S	FEB 27 2025



**EMAGKEC4C4C4C4L
HDX MANAGED**

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	HARDWIRED, CLEARANCE HOLE 1.734" FOR 1.25" CONDUIT	(24) C39 - COMBINATION C13 + C19	UL/cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
69.4" (1764mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V ~ DELTA, 3W + PE 48-100A 50/60Hz 60-125A PANEL BREAKER	200-240V ~ 16A PER C39 16A MAX PER SECTION 48-100A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): EMAGKEC4C4C4C4L	REVISION: 01	EATON
DESCRIPTION: EPDU HDX MA HRDWIRED DELTA 24xC39		SIZE: D		
ORIGINATED BY: SATYAN, S	FEB 27 2025	SEE NOTES FOR TOLERANCES. DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATUS: RELEASED	SCALE: 0.35
MODIFIED BY: SATYAN, S	FEB 27 2025	ECO: CO-0318408	ECO: CO-0318408	SHEET: 1 OF 1

EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT, INCLUDING DRAWINGS AND INFORMATION CONTAINED THEREIN, IS CONFIDENTIAL AND IS THE SOLE PROPERTY OF EATON CORPORATION AND IS RELEASED ON LOAN AND SUBJECT TO BEHALF OF EATON CORPORATION. IT IS TO BE KEPT CONFIDENTIAL AND IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF EATON CORPORATION. ANY UNAUTHORIZED USE, REPRODUCTION, OR DISSEMINATION OF THIS DOCUMENT IS STRICTLY PROHIBITED. THE RECEIPT OF THIS DOCUMENT DOES NOT CONSTITUTE AN ENDORSEMENT OR A WARRANTY BY EATON CORPORATION. THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2025 Eaton Corporation. All Rights Reserved.