



REV	ECO #	DESCRIPTION	DR	DATE
01	CO-0302309	ENGINEERING RELEASE	S.S	APR 03 2025



EMAGMFA5A5A5A5L
HDX MANAGED

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	4100P9W 6FT 4AWG, 4C POWERCORD	(24) C39 - COMBINATION C13 + C19 (24) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
76.0" (1930mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V ~ DELTA, 3W + PE 80A 50/60Hz	200-240V ~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 80A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION 	NAME (PART NUMBER): EMAGMF5A5A5A5A5L	REVISION: 01	EAT-N
DESCRIPTION: EPDU HDX MA 41009PW 24x13 24x39C				SIZE: D
ORIGINATED BY: SATYAN. S	APR 03 2025	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCH) AFTER PLATING INTERFERENT DIM AND TOL FOR ASME Y14.5-2018	STATE: Release	SIZE: 0.100
MODIFIED BY: S. Sangeetha	APR 03 2025		ECC: CO-0302309	SHEET: 1 OF 1
<p><small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO RECIPIENT: THIS DOCUMENT AND/OR TECHNICAL INFORMATION IS UNCLASSIFIED AND NOT CONTROLLED. IT IS THE PROPERTY OF EATON AND IS LOANED TO YOU BY EATON. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT THE WRITTEN PERMISSION OF EATON. IN THE EVENT OF CONFLICTING CONDITIONS, THIS NOTICE SHALL PREVAIL. THE PROOF HEREIN CANNOT BE USED IN THE EVENT OF CONFLICTING CONDITIONS. PROVISIONS, THIS NOTICE SHALL PREVAIL.</small></p>				