




REV	ECO #	DESCRIPTION	DR	DATE
01	CO-0318408	ENGINEERING RELEASE	S.S	FEB 26 2025



EMAGLFC3C3C33L HDX MANAGED

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	IEC 60309 460P9W PLUG 6FT 6AWG, 4C POWERCORD	(12) C39 - COMBINATION C13 + C19 (24) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
69.4" (1764mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V ~ DELTA, 3W + PE 48A 50/60Hz	200-240V ~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 48 MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): EMAGLFC3C3C33L	REVISION: 01	EATON
DESCRIPTION: EPDU HDX MA 460P9W 6FT DEL 24x13, 12xC39		SIZE: D		
ORIGINATED BY: SATYAN, S	FEB 26 2025	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE: Release	SCALE: 0.35
MODIFIED BY: S. Sangamesh	FEB 26 2025	ECO: CO-0318408	SHEET: 1 OF 1	
<small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT IS THE PROPERTY OF EATON CORPORATION AND IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE WRITTEN CONSENT OF EATON. IN THE USE OF CONFIDENTIAL INFORMATION, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2025 Eaton Corporation. All Rights Reserved.</small>				