





REV	ECO #	DESCRIPTION	DR	DATE
01	CO-0302309	ENGINEERING RELEASE	S.S	APR 03 2025



**EMAGMFC2C2C2C2L  
HDX MANAGED**

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	4100P9W 6FT 4AWG, 4C POWERCORD	(48) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
69.4" (1764mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V ~ DELTA, 3W + PE 80A 50/60Hz	200-240V ~ 10A PER C13 16A MAX PER SECTION 80A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

<b>METRIC</b>	THIRD ANGLE PROJECTION	NAME (PART NUMBER): <b>EMAGMFC2C2C2C2L</b>	REVISION: 01	<b>EATON</b>
DESCRIPTION: EPDU HDX MA 4100P9W 6FT UL DELTA 48x13		SIZE: D		
ORIGINATED BY: SATYAN. S	APR 03 2025	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE: Release	SCALE: 0.100
MODIFIED BY: S. Sangamesh	APR 03 2025	ECO: CO-0302309	SHEET: 1 OF 1	
<small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT IS THE PROPERTY OF EATON AND IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE WRITTEN CONSENT OF EATON. IN THE USE OF CONTRACTING PROVISIONS, THIS NOTICE SHALL GOVERN THE TERMS OF THIS DOCUMENT. © 2025 Eaton Corporation. All Rights Reserved.</small>				