



### EMAGMFA5A2A5A2L HDX MANAGED

FUNCTIONALITY	INPUT	OUTPUT	CERTIFICATIONS
CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	4100P9W 6FT 4AWG, 4C POWERCORD	(12) C39 - COMBINATION C13 + C19 (42) IEC C13 GRIP	UL / cUL LISTED
MECHANICAL	INPUT RATING	OUTPUT RATING	CONFIGURATION
76.0" (1930mm) LENGTH 4.1" (104mm) WIDTH 2.5" (63mm) DEPTH ALUMINUM CHASSIS	200-240V ~ DELTA, 3W + PE 80A 50/60Hz	200-240V ~ 10A PER C13, 16A PER C39 80A MAX PER SECTION 48A MAX PER PHASE	
CIRCUIT BREAKERS	ENVIRONMENTAL	ACCESSORIES	
(12) 20A 2-POLE 10KAIC UL LISTED	32° TO 140°F 0° TO 60°C		

METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): <b>EMAGMFA5A2A5A2L</b>	REVISION: 01	<b>EATON</b>
DESCRIPTION: EPDU HDX2 MA 4100P9W 42xC13 12xC39		SIZE: D		
ORIGINATED BY: SATYAN.S	FEB 26 2025	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE: Release	SCALE: 0.35
MODIFIED BY: S. Sangamesh	FEB 26 2025		ECO: CO-0318408	SHEET: 1 OF 1

EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT IS THE PROPERTY OF EATON AND IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE WRITTEN CONSENT OF EATON. IN THE USE OF CONTRACTING PROVISIONS, THIS NOTICE SHALL CONTROL THE TERMS OF THIS DOCUMENT. © 2025 Eaton Corporation. All Rights Reserved.