



EVMOGU23A-E G4 METERED OUTLET

FUNCTIONALITY	INPUT EATON/SOURIAU UTG SERIES 8-PIN CONNECTOR CORDSETS NOT INCLUDED, MUST BE ORDERED SEPARATELY	OUTPUT (12) IEC 60320 C13 (12) EATON C39 - COMBO C13/C19	ENVIRONMENTAL 0° TO 60° C 32° TO 140° F
MECHANICAL	INPUT RATING 1P: 100-240V~, 16-63A, or 3P DELTA: 100-240V~, 16-55A, or 3P WYE: 100-240 / 173-415V~, 16-32A 50/60Hz; USE WITH E21 SERIES CORDSET (CBL3XX-XX)	OUTPUT RATING 100-240V~ 10A PER C13, 16A PER C39 16A MAX PER SECTION NOT TO EXCEED INPUT CORDSET RATING	CERTIFICATIONS cTUVus CE, UKCA, RCM
CIRCUIT BREAKERS	COMMUNICATION G4 eNMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY	ACCESSORIES INCLUDED SPK045 - INSTALLATION OPTIONAL USB-C TO RS232 ADAPTER - U209-006-RJ45XC OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2	REGULATORY MODEL EMOF-ZBAK-G3BK



METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): 9001-22400-EVMOGU23A-E	REVISION:	EATON
DESCRIPTION: PDU G4 MA OU UNV23KW-END 12xC13 12xC39		SIZE: D		
ORIGINATED BY:		SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	STATE:	SCALE: 0.400
MODIFIED BY:			ECO:	SHEET: 1 OF 1
EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT: ANY TECHNICAL INFORMATION CONTAINED HEREIN IS UNCLASSIFIED AND IS NOT TO BE RELEASED TO THE PUBLIC OR TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN CONSENT OF EATON. IN THE CASE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL CONTROL THE TERMS OF THIS AGREEMENT. © Eaton Corporation 2018. All Rights Reserved.				