



Heavy-Duty 2-Post Open Frame Deep Racks

Powering and Connecting Your World

Combine Heavy-Duty Rack Stability with Open Frame Convenience



Tripp Lite's new heavy-duty racks fit conveniently in installations with overhead cable runs.

Perfect for:

Mounting servers, switches and AV and telecommunications equipment in installations with minimal space.

Mount up to 2,000 lb. of IT equipment without sacrificing the convenient access and small footprint of an open frame rack. Tripp Lite's new heavy-duty 2-post open frame deep racks offer 45U of vertical mounting space in a model with 12-in. mounting depth or a model with 24-in. mounting depth.

These racks offer enhanced cable management features, including cable waterfalls, cable hooks, keyhole slots for toolless cable manager mounting and above-rack brackets for mounting a wire basket. The racks can be bolted to the floor, adding stability to a 2-post installation that is easy to install and manage.

Key Benefits

STURDY, HEAVY-DUTY CONSTRUCTION

- Heavy-duty steel construction supports up to 2,000 lb. of equipment.
- Black powder-coated finish is scratch resistant.
- 12-in. or 24-in. extra-deep frame provides added stability.
- Bolt-down provisions enable racks to be fastened to the floor.

ACCESSIBLE OPEN FRAME DESIGN

- Open frame allows fast, easy access for cable installation and maintenance.

CONVENIENT EQUIPMENT MOUNTING

- Racks can mount up to 45U of 19-in., 2-post-compatible rack-mount equipment.
- Numbered 12-24 threaded mounting holes accommodate rack-mount switches, servers and AV and telecommunications equipment.
- Keyhole slots support toolless button-mount installation.

ENHANCED CABLE MANAGEMENT

- Cable waterfall brackets at the top of the rack help reduce stress on cables.
- Side channels have cable tie anchors that accommodate the included cable hooks for efficient cable routing.
- Removable accessory bracket supports wire basket mounting at the top of the rack for compatibility with above-rack cable management systems.

EASY ASSEMBLY AND EXPANSION

- Self-squaring design enables assembly with standard hand tools and the included hardware.
- Expansion-friendly design makes it easy to bolt multiple racks together side by side.

Feature Focus

A Keyhole Slots

The keyhole slots support toolless mounting of 0U/vertical PDUs and cable managers.



B Threaded Mounting Holes

Numbered 12-24 threaded holes make equipment mounting easier.



C Cable Waterfalls

Waterfall brackets maintain a proper bend radius for cables, helping to improve performance and add longevity.



D Cable Hooks

Included hooks fit in cable tie anchors for routing cables neatly alongside the rack channels.



E Accessory Bracket

The accessory bracket can support a wire basket or other cable management system atop the rack.



F Bolt-Down Provisions


Base plates have 4 bolt provisions for fastening the rack to the floor.



G Expandability

Multiple racks can be bolted together side-by-side for convenient expansion.

Extra Deep Frame



Model: SR2POSTDP24HD

SPECIFICATIONS

Model	SR2POSTDP12HD	SR2POSTDP24HD
Depth	12 in.	24 in.
Rack Units	45U	45U
Mounting Posts	2	2
Mounting Hole Thread Size	12-24	12-24
Side-by-Side Expansion	Yes	Yes
Weight Supported	2,000 lb. (907 kg)	2,000 lb. (907 kg)
Dimensions (HxWxD)	85.8 x 20.3 x 13.5 in. (2180 x 516 x 343 mm)	85.8 x 20.3 x 26.0 in. (2180 x 516 x 660 mm)
Unit Weight	91.7 lb. (41.6 kg)	134 lb. (60.8 kg)



Learn more about Tripp Lite's full line of server racks and cabinets at tripplite.com.



Tripp Lite Corporate Headquarters
1111 West 35th Street, Chicago, IL 60609 USA
773.869.1773 | tripplite.com