



D



C




B

EVMi2120X G4 METERED INPUT

FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT, POWER, AND ENERGY METERING FOR INPUT; CURRENT METERING FOR BRANCH	NEMA L21-30 10AWG / 5C 10FT POWERCORD	(24) IEC 60320 C13 (18) EATON C39 - COMBO C13/C19	0° TO 60° C 32° TO 140° F
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
68.11" (1730mm) LENGTH 2.05" (52mm) WIDTH 2.09" (53mm) DEPTH ALUMINUM CHASSIS, BLACK	100-127 / 173-240V ~ WYE, 3W + N + PE 16A 50/60HZ	173-240V ~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 16A MAX PER PHASE	cTUVus
CIRCUIT BREAKERS	COMMUNICATION	ACCESSORIES	REGULATORY MODEL
(3) 20A 2-POLE LISTED	G4 eNMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY	INCLUDED SPK045 - INSTALLATION OPTIONAL USB-C TO RS232 ADAPTER - U209-006-RJ45XC OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2	EMIF-PBXJ-E27K

A



METRIC

THIRD ANGLE PROJECTION

NAME (PART NUMBER):

9001-22314_EVMi2120X

REVISION:

EATON

DESCRIPTION:

PDU G4 MI 0U L21-20P 24xC13,18xC39

SIZE: D

ORIGINATED BY:

SEE NOTES FOR TOLERANCES
DIM ARE IN MM (INCHES) AFTER PLATING

STATE:

SCALE: 0.400

MODIFIED BY:

INTERPRET DIM AND TOL PER ASME Y14.5-2019

ECO:

SHEET: 1 OF 1

©2024 Eaton. All rights reserved.