



<div><div>B</div><div>EVMi4609X-06 G4 METERED INPUT</div></div>				<div><div>B</div><div></div></div>			
FUNCTIONALITY		INPUT	OUTPUT	ENVIRONMENTAL			
CURRENT, POWER, AND ENERGY METERING FOR INPUT; CURRENT METERING FOR BRANCH		IEC 60309 460P9W 6AWG / 4C 6FT POWERCORD	(24) IEC 60320 C13 (18) EATON C39 - COMBO C13/C19	0° TO 60° C 32° TO 140° F			
MECHANICAL		INPUT RATING	OUTPUT RATING	CERTIFICATIONS			
72.01" (1829mm) LENGTH 2.05" (52mm) WIDTH 2.56" (65mm) DEPTH ALUMINUM CHASSIS, BLACK		200-240V ~ DELTA, 3W + PE 48A 50/60HZ	200-240V ~ ; 10A PER C13, 16A PER C39 16A MAX PER SECTION 48A MAX PER PHASE	cTUVus			
CIRCUIT BREAKERS		COMMUNICATION	ACCESSORIES	REGULATORY MODEL			
(6) 20A 2-POLE LISTED		G4 eNMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY	INCLUDED SPK045 - INSTALLATION OPTIONAL USB-C TO RS232 ADAPTER - U209-006-RJ45XC OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2	EMIF-FL6J-G28K			

A

A

THIRD ANGLE PROJECTION

NAME (PART NUMBER):

REVISION:

METRIC

9001-22302\_EVMi4609X-06

EATON

DESCRIPTION:

ORIGINATED BY:

MODIFIED BY:

SEE NOTES FOR TOLERANCES  
DIM ARE IN MM (INCHES) AFTER PLATING  
INTERPRET DIM AND TOL PER ASME Y14.5-2019

STATE:

ECO:

SIZE: D

SCALE: 0.400

SHEET: 1 OF 1

©2024 Eaton. All rights reserved.