



## NEW PRODUCT ANNOUNCEMENT

### Heavy-Duty Security Wall Mounts

# Deter Theft of Public Displays with Security Wall Mounts



Model: DWFSC3780MUL



*Included combination lock secures the solid steel security bar.*

#### Perfect for:

Hotels, bars, restaurants, shopping malls, libraries, schools, hospitals and airports.

Tripp Lite's security mounts have special features to discourage theft of wall-mounted televisions and monitors. A solid steel security bar and the included combination lock work together to secure the vertical brackets to the wall plate. The security bar slides through the brackets, and the lock fastens the bar in place, preventing easy removal of the display. The mounts also have end caps and recessed set screws for additional security.

Designed to accommodate flat and curved screens, the mounts bring security to installations in public areas where displays are vulnerable to theft and tampering.

### Key Benefits

#### THEFT DETERRENCE

- Heavy-duty powder-coated steel construction offers ruggedness and durability.
- Solid steel bar and three- or four-position combination lock prevent easy removal of the display.
- End caps and recessed set screws offer extra protection against tampering.

#### VIEW OPTIMIZATION

- Mounts are available to accommodate flat and curved displays up to 80 inches.
- Fixed, tilt and full-motion styles make the most of every display environment.

#### EASY INSTALLATION

- Brackets are compatible with VESA mounting hole patterns on displays.
- Built-in bubble level facilitates even alignment.
- Open frame provides access to cables.
- Mounting hardware is included.

#### PROFESSIONAL APPEARANCE

- The security features are hidden behind the display, maintaining a polished look.

## Feature Focus


### Security Bar and Combination Lock

The included combination lock prevents the solid steel security bar from being removed from the display brackets.



### Built-In Bubble Level

The wall plate has a built-in level to aid alignment during installation.



### Open Frame

An open frame design provides easy access to cables.



### VESA-Compliant Brackets

The brackets are compatible with mounting hole patterns on VESA-compliant displays.

### Tilt Adjustment (DWTSC3255MUL & DWTSC3780MUL)

The tilt adjustment minimizes glare and improves viewing angles, especially where the audience is below the display.



### Full-Motion Adjustment (DWMSC3780MUL)

Swivel, tilt and screen level adjustments offer the most options for view optimization.



## SPECIFICATIONS

Model	DWFSC3255MUL	DWTSC3255MUL	DWFSC3780MUL	DWTSC3780MUL	DWMSC3780MUL
<b>Motion</b>	Fixed	Tilt	Fixed	Tilt	Full Motion
<b>Supported Screen Sizes</b>	32 to 55 in.	32 to 55 in.	37 to 80 in.	37 to 80 in.	37 to 80 in.
<b>Weight Capacity</b>	99 lb./150 lb.*	99 lb./150 lb.*	88 lb./200 lb.*	88 lb./200 lb.*	88 lb./200 lb.*
<b>Mounting Profile (Surface to Display)</b>	1 in.	2 in.	0.9 in.	2 in.	21.6 in. (fully extended)
<b>Supported VESA Patterns</b>	200x200, 300x300, 400x200, 400x400	200x200, 300x300, 400x200, 400x400	300x300, 400x200, 400x400, 600x400	300x300, 400x200, 400x400, 600x400	300x300, 400x200, 400x400, 600x400, 800x400
<b>Tilt Adjustment</b>	—	-15° to +10°	—	-10° to +5°	-10° to +5°
<b>Swivel Adjustment</b>	—	—	—	—	±90°
<b>Screen Level Adjustment</b>	—	—	—	—	-4° to +4°
<b>Construction</b>	Powder-Coated Steel				
<b>Combination Lock</b>	Three Position	Three Position	Four Position	Four Position	Four Position
<b>Warranty</b>	5-Year Limited				

All mounts comply with RoHS standards. \* Function- and weight-tested to higher value in accordance with UL 2442.

Learn more about Tripp Lite's full line of display mounts at [www.triplite.com](http://www.triplite.com).



Tripp Lite Corporate Headquarters

1111 W. 35th Street, Chicago, IL 60609  
773.869.1773 • [www.triplite.com](http://www.triplite.com)