

### Make any space a high-performance workstation



Mobile workstations and display mounts are fully compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

#### Perfect for:

Mobile medical documentation, creative collaboration and dynamic sales presentations.

TAA-compliant mobile workstations and display mounts help healthcare and business professionals make hectic, unpredictable workspaces more manageable. These feature-rich solutions include three mobile workstation carts that can easily relocate medical IT and other electronics within a room or throughout a building.

The ivory color of these mobile workstations makes them fit seamlessly in healthcare settings or with light-colored, contemporary office décor. A desk clamp model holds either a laptop or a notebook in one arm and a 17 to 32 in. monitor in the other arm, creating a dynamic workstation where desktop surface space is limited. Their TAA compliance makes them eligible for purchase by government agencies and government contractors.

#### Key benefits

##### TAA COMPLIANCE

- All parts and accessories are TAA compliant for GSA schedule purchases.

##### CONVENIENT WORKSPACE ENHANCEMENTS

- Smooth-rolling casters on mobile workstations make it easy to relocate IT equipment and maximize usage; caster locks easily fix the cart in place.
- Cable access ports or management brackets on select models help organize cords and prevent clutter.
- Drawers on select models conveniently store electronics and other items when not in use; the locking drawer on WWSS1DWSTAA deters theft.
- Built-in mouse pads fold neatly into the unit to preserve desk space (WWSS2DWSTAA and WWSS1DWSTAA only).



##### BROAD COMPATIBILITY

- Adjustable-height desktop and shelves on mobile workstations help end users work in comfort.
- Full-motion display mounting arm and computer mounting arm on the desk clamp model (DDR1732NBMTAA) position a monitor and a computer, respectively, at optimal angles.
- Mounting arms support 75x75 and 100x100 (DDR1732NBMTAA) and 75x75, 75x100, 100x75 and 100x100 (WWSS1DWSTAA) VESA mounting patterns.

##### PROTECTIVE DESIGN


- Models are built to last in any environment.
- Vented aluminum laptop tray on DDR1732NBMTAA helps prevent a mounted computer from overheating.
- WWSS1DWSTAA's keyboard tray slides under the desk surface when not in use to preserve space and protect the keyboard from damage.

## Feature focus


- A** Single (WWSS1DWSTAA) or dual (WWSS2DWSTAA) mouse pads slide beneath the top work surface when not in use.
- B** One or two drawers store supplies. Drawer on WWSS1DWSTAA locks for added security.
- C** Support post(s) have built-in tracks for easy up/down adjustment of shelves\*.
- D** Adjustable MDF shelves can be removed\*\*.
- E** Cable access ports.
- F** Locking 4 in. swivel casters.
- G** Keyboard tray slides under the work surface when not in use.
- H** Perforated aluminum laptop tray helps keep a mounted computer cool.
- I** VESA-compliant mounting bracket swivels, tilts and rotates a screen for optimal viewing angles.
- J** Tension adjusters tighten or loosen mounting brackets.
- K** Cable managers.
- L** Toolless adjustment handles.

\* Adjustable brackets/shelves can be positioned anywhere along the full length of the post(s).  
 \*\* The bottom shelf on WWSS2DWSTAA and WWSSRSTAA and the base on WWSS1DWSTAA are not adjustable.


### Mobile workstations



### Mobile workstation with mounting arm



### Desk clamp



## SPECIFICATIONS

Mobile workstations	WWSS1DWSTAA	WWSS2DWSTAA	WWSSRSTAA
Model			
Adjustable shelves / drawers	1 / 1	2 / 2	3 / —
Supported screen sizes	Up to 24 in.	—	—
Weight capacity	11 lb. per adjustable shelf; 15 lb. monitor; 6 lb. drawer	11 lb. per adjustable shelf; 6 lb. per drawer	11 lb. per adjustable shelf
Screen swivel / tilt	360° / +60°	—	—
VESA pattern (mm)	75x75, 75x100, 100x75, 100x100	—	—
Primary construction	Steel with MDF shelf	Steel with MDF shelves	Steel with MDF shelves
Unit dimensions (H x W x D)	60 (at max. height) x 24 x 21.6 in.	43.1 x 26 x 23.9 in.	43.1 x 26 x 23.9 in.
Unit weight	96.8 lb.	85.6 lb.	70.2 lb.
Desk clamp	DDR1732NBMTAA		
Model			
Quantity of supported devices	2		
Supported screen sizes	Laptop/notebook: up to 15 in.; Monitor: 17 to 32 in.		
Weight capacity	12.2 lb. (for 2 mounted devices combined)		
Screen adjustment	Laptop/notebook: +/-20° tilt; Monitor: 360° swivel, 360° rotate, +/-180° tilt		
VESA pattern (mm)	75 x 75; 100 x 100		
Unit dimensions (H x W x D)*	24.8 x 15.8 x 23.4 in.		
Unit weight	20.2 lb.		

All models have a 5-year limited warranty.

Learn more about our full line of workstation solutions at [tripplite.eaton.com](http://tripplite.eaton.com).

**TRIPP·LITE**  
by **EAT·N**