



Solutions for Resident Rooms in Long-Term Care Facilities



Resident safety depends on compliance with regulations that govern the use of power strips in long-term care facilities.

With the adoption of the 2012 edition of the National Fire Protection Association® (NFPA) 101 - Life Safety Code (LSC) and the NFPA 99 - Health Care Facilities Code (HCFC), the Centers for Medicare and Medicaid Services (CMS) now allows power strips in resident rooms of long-term care facilities. This includes nursing-home and assisted-living-facility rooms that do not use line-operated electrical appliances for diagnostic, treatment or monitoring purposes (patient care vicinities).

Our products include hospital-grade plugs and outlets that meet UL 1449 (3rd Ed.) and UL 1363 standards and are now allowed by CMS. These surge protectors and power strips are ideal for use with lamps, phone chargers, radios, TVs, stereos, PCs, printers and video game systems.

Specifications

Model	Nominal AC Voltage/Amps	UL Compliance	Surge Protection Rating	AC Outlets	AC Input Cord Length	AC Input Plug Type
Hospital-Grade Surge Protectors (For use outside patient care vicinities only.)						
ISOBAR6ULTRAHG	120V/12A	UL 1363 & UL 1449 (3rd Ed.)	3,330 joules	6 (5-15R HG)	15 ft.	5-15P HG
SPS-615-HG	120V/15A	UL 1363 & UL 1449 (3rd Ed.)	1,050 joules	6 (5-15R HG)	15 ft.	5-15P HG
SPS610HGRA	120V/15A	UL 1363 & UL 1449 (3rd Ed.)	1,050 joules	6 (5-15R HG)	10 ft.	5-15P HG (Right Angle)
SPS606HGRA	120V/15A	UL 1363 & UL 1449 (3rd Ed.)	1,050 joules	6 (5-15R HG)	6 ft.	5-15P HG (Right Angle)
Hospital-Grade Power Strips (For use outside patient care vicinities only.)						
PS-615-HG	120V/15A	UL 1363	n/a	6 (5-15R HG)	15 ft.	5-15P HG
PS-606-HG	120V/15A	UL 1363	n/a	6 (5-15R HG)	6 ft.	5-15P HG
PS-602-HG	120V/15A	UL 1363	n/a	6 (5-15R HG)	1.5 ft.	5-15P HG
PS-415-HG	120V/15A	UL 1363	n/a	4 (5-15R HG)	15 ft.	5-15P HG

Hospital-grade solutions are suitable for use outside patient care vicinities. Certifications vary by model. Go to www.tripplite.com for more information, including weights, dimensions and updates.

If you don't see what you're looking for, visit www.tripplite.com for over 200 other power strips that meet UL 1363 standards

For solutions approved for use in patient care vicinities, please see other side.



CMS Adopts New Codes for Power Strip Use in Patient Care Vicinities

On July 5, 2016, CMS adopted by regulation the 2012 edition of the LSC and NFPA 99.* These regulations allow the use of power strips in patient care vicinities in new and existing healthcare facilities, if the provider/supplier meets all of the listed requirements.

As the leader in healthcare power solutions, Tripp Lite provides products that meet or exceed the requirements outlined in the 2012 edition of the LSC and NFPA 99.



Specifications

Model	Nominal AC Voltage/Amps	UL Compliance	Surge Protection Rating	AC Outlets	AC Input Cord Length	AC Input Plug Type
Medical-Grade Power Strips for Patient Care Vicinities						
NEW PS-406-HGULTRA	120V/15A	UL 60601-1 ⁽¹⁾	n/a	4 (5-15R HG)	6 ft.	5-15P HG
PS-415-HGULTRA	120V/15A	UL 60601-1 ⁽¹⁾	n/a	4 (5-15R HG)	15 ft.	5-15P HG
SPS415HGULTRA	120V/15A	UL 60601-1 ⁽¹⁾	1,410 joules	4 (5-15R HG)	15 ft.	5-15P HG
OEM-Series Power Strips for Mobile Applications In Patient Care Vicinities (Specialty-Purpose Relocatable Power Strips)						
PS615HG20AOEM	120V/20A	UL 1363A	n/a	6 (5-15/20R HG)	15 ft.	5-20P HG
PS625HG20AOEM	120V/20A	UL 1363A	n/a	6 (5-15/20R HG)	25 ft.	5-20P HG
PS-615-HG-OEM	120V/15A	UL 1363A	n/a	6 (5-15R HG)	15 ft.	5-15P HG
PS-415-HG-OEM	120V/15A	UL 1363A	n/a	4 (5-15R HG)	15 ft.	5-15P HG
PS-410-HGOEMCC	120V/15A	UL 1363A	n/a	4 (5-15R HG)	3 to 10 ft. ⁽²⁾	5-15P HG
PS410HGOEMX	120V/15A	UL 1363A	n/a	4 (5-15R HG)	10 ft.	5-15P HG
Hospital-Grade Surge Protectors for Administrative Vicinities^(3,5) (Relocatable Power Strips with Surge Protection)						
ISOBAR6ULTRAHG	120V/15A	UL 1363 & UL 1449 (3rd Ed.)	3,330 joules	6 (5-15R HG)	15 ft.	5-15P HG
SPS-615-HG	120V/15A	UL 1363 & UL 1449 (3rd Ed.)	1,050 joules	6 (5-15R HG)	15 ft.	5-15P HG
SPS606HGRA	120V/15A	UL 1363 & UL 1449 (3rd Ed.)	1,050 joules	6 (5-15R HG)	6 ft. ⁽⁴⁾	5-15P HG (Right Angle)
SPS610HGRA	120V/15A	UL 1363 & UL 1449 (3rd Ed.)	1,050 joules	6 (5-15R HG)	10 ft. ⁽⁴⁾	5-15P HG (Right Angle)
Accessories						
PSCLAMP	Pre-Assembled Locking Pole Mount Clamp. Compatible with Tripp Lite Medical-Grade Power Strips. Fits a diameter from 1" to 2¼"					
HGOUTLETCVR	Reusable locking safety covers prevent the connection of unauthorized devices—tool required for removal. Compatible with all NEMA 5-15R HG receptacles.					

All models have nominal 120V input/output, hospital-grade plug and hospital-grade outlets. Agency approved to UL standard shown; additional certifications vary by model. (1) Meets the standards of a medical device when installed properly. (2) Coiled cord. (3) Also suitable for use in other areas outside patient care vicinities. (4) Right-angle plug. (5) The models listed here are suggestions. Any hospital-grade solution in this flyer can be used in Administrative Areas.

For more information, contact:



1111 W. 35th Street, Chicago, IL 60609 USA • 773.869.1282 • medical@tripplite.com • www.tripplite.com

* To access the full document, go to www.cms.gov/Medicare/Provider-Enrollment-and-Certification/SurveyCertificationGenInfo/Downloads/Survey-and-Cert-Letter-16-29.pdf
 Copyright © 2016 Tripp Lite. All trademarks are the sole property of their respective owners. Photos and illustrations may differ slightly from actual products. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Life-Support Statement: Tripp Lite does not recommend the use of any of its products in any life-support application in which a malfunction or failure of a Tripp Lite product could cause failure or significantly alter the performance of a life-support device.