

## Smart 116 IP - 16-Port, Remote Access Cat5 KVM Switch for Rack Environments

MODEL NUMBER: 0SU70030



### Description

Local or remote access to servers in the data center

Ideal for branch offices and growing companies

Industry standard security

BIOS level, mixed platform access

### Features

- 16 Ports
- Remote or Local Access
- BIOS level access
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cable
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

## Specifications

### Highlights

- 16 Ports
- Remote or Local Access
- BIOS level access
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cable
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

### System Requirements

#### Operating System

- Host & Remote: Windows, Linux

#### Resolution

- Target Server: 1600 x 1200 @ 85Hz
- Client Computer: Recommended that resolution should be higher than local computer resolution

#### Package Includes

- Smart 116 IP Cat5 KVM Switch
- RS232 Download Cable
- Rackmount Kit
- Owner's Manual

| <b>OVERVIEW</b>                      |                              |
|--------------------------------------|------------------------------|
| UPC Code                             | 654518209303                 |
| Console                              | No                           |
| <b>PHYSICAL</b>                      |                              |
| Color                                | Black                        |
| Shipping Dimensions (hwd / in.)      | 5.00 x 1.08 x 1.66           |
| Shipping Dimensions (hwd / cm)       | 12.70 x 2.74 x 4.22          |
| Shipping Weight (lbs.)               | 7.70                         |
| Shipping Weight (kg)                 | 3.49                         |
| Unit Dimensions (hwd / in.)          | 1.600 x 17.000 x 9.100       |
| Unit Dimensions (hwd / cm)           | 4.1 x 43.1 x 23              |
| Unit Weight (lbs.)                   | 5.6                          |
| Unit Weight (kg)                     | 2.54                         |
| <b>ENVIRONMENTAL</b>                 |                              |
| Storage Temperature Range            | -40 to 70 C / -40 to 158 F   |
| Operating Temperature                | 0 to 40 C / 32 to 104 F      |
| <b>COMMUNICATIONS</b>                |                              |
| Port Control                         | Hotkeys, OSD, Remote Toolbar |
| IP Remote Access                     | Yes                          |
| <b>CONNECTIONS</b>                   |                              |
| Number of Ports                      | 16                           |
| PC/Server Connections                | VGA; USB; PS/2               |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                              |
| Cat5 KVM Switch                      | Yes                          |
| NIAP-Certified Secure                | No                           |
| Number of Users                      | 1                            |
| <b>WARRANTY &amp; SUPPORT</b>        |                              |
| Product Warranty Period (Worldwide)  | 3-year limited warranty      |



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.