

Minicom Smart 216 IP - 16-Port Multi-User, Remote Access Cat5 KVM Switch for Rack Environments

MODEL NUMBER: 0SU70036



Description

Simultaneous remote and local access to servers

From server rooms to data centers

KVM IP power control

Industry standard security protocol

Absolute mouse support

Features

- 16 Ports
- 3 simultaneous KVM Users (2 remote and 1 local)
- 2 additional serial session users
- Control the power of your servers remotely through seamless integration with any Smart PDU (SNMP)
- BIOS level access

Highlights

- 16 Ports
- 3 simultaneous KVM Users (2 remote and one local)
- 2 additional serial session users
- BIOS level access
- USB keyboard and mouse console
- Absolute mouse support
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cable
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

System Requirements

Operating System

- Target Server: Windows, Novell, Linux, SUN Solaris
- Client Computer: Windows 2000 or higher with IE 6.0 or higher and ActiveX

Resolution

- Target Server: 1600 x 1200 @ 85Hz
- Client Computer: Recommended that resolution should be higher than local computer resolution

Package Includes

- Smart 216 IP Cat5 KVM Switch
- RS232 Download Cable
- Rackmount Kit
- Owner's Manual



Powering Business Worldwide



- USB keyboard and mouse console
- Absolute mouse support
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cable
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

Specifications

OVERVIEW	
UPC Code	654518209938
CONNECTIONS	
Number of Ports	16
Computer/Server Ports	16
PC/Server Connections	USB; PS/2; VGA; Serial
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	5.00 x 1.08 x 1.66
Shipping Dimensions (hwd / cm)	12.70 x 2.74 x 4.22
Shipping Weight (lbs.)	7.70
Shipping Weight (kg)	3.49
Unit Dimensions (hwd / in.)	1.700 x 17.000 x 10.600
Unit Dimensions (hwd / cm)	4.4 x 43.1 x 27
Unit Weight (lbs.)	5.165
Unit Weight (kg)	2.34
ENVIRONMENTAL	
Storage Temperature Range	-40 to 70 C / -40 to 158 F
Relative Humidity	80% Non-Condensing
Operating Temperature	0 to 40 C / 32 to 104 F
COMMUNICATIONS	
Port Control	Hotkeys, OSD, Remote Toolbar
IP Remote Access	Yes
FEATURES & SPECIFICATIONS	
NIAP-Certified Secure	No
Number of Users	3

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.