



Powering Business Worldwide

9PX 192V Lithium-Ion Extended Battery Module (EBM) for 9PX6KG2-L, 9PX8KG2-L and 9PX11KG2-L UPS Systems, 2U Rack/Tower

MODEL NUMBER: 9PXEBM192RTG2-L



Lithium-ion extended battery module (EBM) provides more runtime for compatible Eaton 9PX G2 UPS systems.

Features

Backup Battery Module Gives Your Compatible Eaton UPS System Extended Runtime

The lithium-ion 9PXEBM192RTG2-L offers extended battery runtime when used in conjunction with Eaton's 9PX6KG2-L, 9PX8KG2-L or 9PX11KG2-L UPS system. It can also be daisy-chained for a maximum of 10 matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

Supports 2U Rack or Tower Installation

This lithium-ion backup battery pack is smaller and lighter than VRLA modules. Its multi-use form factor supports mounting in 2U of space in EIA-standard 19-inch open frame racks or enclosures using the included 4-post rail kit and mounting brackets. Tower stands from a compatible UPS support optional upright configuration of the battery pack. For 2-post rack mounting, an optional RK2PC mounting kit (sold separately) is required for each UPS, EBM, PPDM or transformer.

Specifications

OVERVIEW	
UPC Code	786689972790
UPS Type	On-Line
INPUT	
Input Phase	Single-Phase
OUTPUT	
Individually Controllable Load Banks	No

Highlights

Connects to expandable 6kVA–11kVA 9PX G2 UPS system for extended runtimeImproved lithium-ion batteries have lifespan up to 10 years - set it and forget itDaisy-chain connector supports additional battery packs for even longer runtimeIncludes heavy-gauge cabling with high-current 192V DC connectorsSupports 2U rack mounting or upright tower installation

System Requirements

Compatible with Eaton's 9PX6KG2-L, 9PX8KG2-L and 9PX11KG2-L UPS systems

Package Includes

- 192V Lithium-Ion Extended Battery Module
- External battery cable, 1 ft. (0.3 m)
- Rack-mounting hardware
- Quick Start Guide



Powering Business Worldwide

BATTERY	
Battery Type	Lithium-ion (LiFePO4)
Expandable Runtime	Yes
Expandable Runtime Description	Add up to 10 extended battery modules (EBMs)
DC System Voltage (VDC)	192
Battery Replacement Description	Internal EBM batteries are not replaceable (replace entire EBM). Extended battery modules (EBMs) are hot-swappable.
Internal Battery Details	192V 12Ah 2304Wh
Battery Management	Integrated battery management system (BMS) for temperature regulation and life cycle monitoring
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	2U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (RK2PC)
Minimum Required Rack Depth (cm)	73.66
Minimum Required Rack Depth (inches)	29
Unit Dimensions (hwd / in.)	3.360 x 17.240 x 25.390
Unit Weight (lbs.)	77
Unit Weight (kg)	34.93
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-96% non-condensing
CARTON FILES	
Carton Notes	Pallet dims: 48in*40in*43in. (6/pallet)
STANDARDS & COMPLIANCE	
Product Certifications	EN 62040-2; NOM (Mexico); cUL Listed
Product Compliance	CE (Europe); FCC (USA); FCC Part 15 Class A (USA); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	5-year limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.