



Powering Business Worldwide

# Eaton 9PX 192V Lithium-Ion Extended Battery Module (EBM) for 9PX6K-L UPS System, 2U Rack/Tower

MODEL NUMBER: 9PXEBM192RT-L



Lithium-ion extended battery module (EBM) provides more runtime for the Eaton 9PX6K-L UPS system.

## Features

### Backup Battery Module Gives Your Compatible Eaton UPS System Extended Runtime

The 9PXEBM192RT-L offers extended battery runtime when used in conjunction with Eaton's 9PX6K-L UPS system. It can also be daisy-chained for a maximum of four matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

### Supports 2U Rack or Tower Installation

This backup battery pack's multi-use form factor supports mounting in 2U of space in EIA-standard 19-inch open frame racks or enclosures using the included 4-post rail kit and mounting brackets. Tower stands from a compatible UPS support optional upright configuration of the battery pack. For 2-post rack mounting, an optional RK2PC mounting kit (sold separately) is required for each UPS, EBM, PPDM or transformer.

## Specifications

OVERVIEW	
UPC Code	786689772574
UPS Type	On-Line
INPUT	
Input Phase	Single-Phase
OUTPUT	
Individually Controllable Load Banks	No

## Highlights

- Connects to expandable 9PX6K-L UPS system for extended runtime
- Daisy-chain connector supports additional battery packs for even longer runtime
- Includes heavy-gauge cabling with high-current 192V DC connectors
- Supports 2U rack mounting or upright tower installation

## System Requirements

Compatible only with Eaton's 9PX6K-L UPS system

## Package Includes

- 192V Lithium-Ion Extended Battery Module
- External battery cable, 1 ft. (0.3 m)
- Rack-mounting hardware
- Quick Start Guide



Powering Business Worldwide

BATTERY	
Battery Type	Lithium-ion (LiFePO4)
Expandable Runtime	Yes
Expandable Runtime Description	Add up to 4 extended battery modules (EBMs)
DC System Voltage (VDC)	192
Battery Replacement Description	Hot-swappable internal batteries and extended battery modules (EBMs)
Battery Management	Integrated battery management system (BMS) for temperature regulation and life cycle monitoring
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	2U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (&nbsp;<a class="productLink" href="//tripplite.eaton.com/eaton-2-post-rack-mount-rail-kit-for-9px-ups~RK2PC">RK2PC</a>&nbsp;)
Minimum Required Rack Depth (cm)	73.66
Minimum Required Rack Depth (inches)	29
Unit Dimensions (hwd / in.)	3.360 x 17.240 x 25.390
Unit Weight (lbs.)	79.0
Unit Weight (kg)	35.83
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-96% non-condensing
CARTON FILES	
Carton Notes	Pallet dims: 48in*40in*43in. (6/pallet)
STANDARDS & COMPLIANCE	
Product Certifications	EN 62040-2; NOM (Mexico); cUL Listed
Product Compliance	CE (Europe); FCC (USA); FCC Part 15 Class A (USA); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	5-year limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.