




Powering Business Worldwide

9PX G2 PowerPass Distribution Module for 3kVA to 6kVA 9PX G2 UPS Systems, Hardwire Input/Output, 3U Rack/Tower

MODEL NUMBER: 9XPPDM2G2



Converts 208V UPS input to 120V for powering low-voltage AC components and transfers UPS power to utility during UPS maintenance or replacement.

Features

208V to 120V Power Distribution Module Converts High-Voltage Input to Low-Voltage Output

The 9XPPDM2G2 converts your UPS system's 208V high-voltage input to 120V low-voltage output. It features hardwired input and output for connecting equipment and resettable 30A circuit breakers that protect against overload conditions.

Compatible with Select Eaton UPS Systems

The 9XPPDM2G2 works with Eaton's 9PX5KG2, 9PX6KG2, 9PX6K-L and 9PX3K3UG2 9PX G2 UPS systems. Its front-panel maintenance bypass switch lets you service or replace the UPS system without powering down any equipment and risking costly downtime. All connected equipment remains energized, even while the UPS system is not present.

Versatile Installation Options

You can mount the 9XPPDM2G2 in 3U of space in an EIA-standard 19-inch rack using the included 4-post rail kit or an optional 2-post rail kit (RK2PC, sold separately). You can also adapt it for tower installation using the included joining bracket and hardware.

Specifications

OVERVIEW	
UPC Code	786689876043
Accessory Type	Power Module
Accessory Class	UPS Accessories
INPUT	
Input Phase	Single-Phase

Highlights

- Converts high-voltage AC output into low voltage for powering low-voltage equipment
- Provides extra protection against power spikes and surges that can damage equipment
- Resettable circuit breakers protect connected equipment from hazardous overloads
- Maintenance bypass allows UPS service or replacement without powering down load

System Requirements

Compatible with Eaton's 9PX5KG2, 9PX6KG2, 9PX6K-L and 9PX3K3UG2 UPS systems

Package Includes

- 9XPPDM2G2 PowerPass Distribution Module
- (2) Cable glands
- Joining bracket and hardware for tower configuration
- Rack-mounting hardware
- User's Guide



Powering Business Worldwide

UPS Input Connection Type	Hardwire
Input Plug Type	Hard-wire
OUTPUT	
Output Capacity (VA)	6000
Output Capacity (kVA)	6
Output Capacity (Watts)	6000
Output Capacity (kW)	6
Frequency Compatibility	50 / 60 Hz
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	100V; 110V; 120V; 208V; 220V; 230V; 240V
Output Receptacles	(1) Hardwire
Individually Controllable Load Banks	No
BATTERY	
Expandable Runtime	No
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	3U
Unit Dimensions (hwd / in.)	5.100 x 17.300 x 26.930
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico)
Product Compliance	CE (Europe); ENERGY STAR Qualified; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.