

# Eaton 9PX 10kVA 120V Stepdown Transformer - 8 NEMA 5-20R, 2 L14-30R Outlets, 50/60 Hz, Hardwire Input, 3U Rack/Tower

MODEL NUMBER: 9PXTFMR11



10kVA transformer converts UPS 208V input to 120V for powering low-voltage AC components.

## Features

### 208V to 120V Isolation Transformer Converts High-Voltage Input to Low-Voltage Output

This 10kVA Stepdown Transformer converts your UPS system's 208V high-voltage input to 120V low-voltage output. It features eight NEMA 5-20R and two L14-30R outlets for connecting equipment. Resettable circuit breakers protect your 120V equipment against overload conditions. The 9PXTFMR11 works with Eaton's 8kVA to 11kVA 9PX UPS systems.

### Versatile Installation Options

You can mount the 9PXTFMR11 in 3U of space in an EIA-standard 19-inch rack using the included 4-post rail kit. You can also adapt it for tower installation using the included joining bracket and hardware.

## Specifications

| OVERVIEW                  |                       |
|---------------------------|-----------------------|
| UPC Code                  | 743172039323          |
| Accessory Type            | Isolation Transformer |
| Accessory Class           | UPS Accessories       |
| INPUT                     |                       |
| UPS Input Connection Type | Hardwire              |
| Plug Type                 | Hard-wire             |
| Input Phase               | Single-Phase          |

## Highlights

- Converts 208V AC input into 120V output for powering low-voltage equipment
- 8 NEMA 5-20R 120V outlets for connecting components with 5-15P or 5-20P plugs
- Resettable circuit breakers protect mission-critical equipment from hazardous overloads
- Requires hardwired connection to Eaton 9PX 8kVA to 11kVA UPS systems

## System Requirements

Compatible with Eaton's 8kVA to 11kVA 9PX UPS systems

## Package Includes

- 9PXTFMR11 10kVA 120V Stepdown Transformer
- Transformer cable
- (2) Cable glands
- Joining bracket and hardware for tower configuration
- Rack-mounting hardware
- Owner's manuals



Powering Business Worldwide

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

| OUTPUT                                  |   |
|---|---|
| Individually Controllable Load Banks    | No  |
| BATTERY                                 |   |
| Expandable Runtime                      | No  |
| PHYSICAL                                |   |
| Primary Form Factor                     | Rackmount; Tower  |
| Rack Height                             | 3U  |
| Unit Dimensions (hwd / in.)             | 23.430 x 12.720 x 38.460  |
| ENVIRONMENTAL                           |   |
| Operating Temperature Range             | 0° to 40°C (32° to 104°F)   |
| Relative Humidity                       | 0-95% non-condensing  |
| STANDARDS & COMPLIANCE                  |   |
| Product Certifications                  | cUL Listed; NOM (Mexico)  |
| Product Compliance                      | CE (Europe); ENERGY STAR Qualified; RoHS  |
| WARRANTY & SUPPORT                      |   |
| Product Warranty Period (U.S. & Canada) | 2-year limited warranty   |
| Extended Service Plans                  | <b>ADVANCED DEPOT EXCHANGE</b> 5-YEAR DEPOT REPAIR: 9SW5Y-11000UCExpedited parts coverage for 5 yearsParts, electronics and UPS batteries coverageNext business day shippingTechnical support <b>ON-SITE 24x7, NEXT DAY RESPONSE</b> 2 YEAR UPGRADE: WUN72XXX-11000UCOn-site expedited parts and labor coverage for first 2 yearsParts, electronics and UPS batteries coverageEaton on-site labor coverage24x7 coverage, next day responseNext day shippingTechnical support <b>3 YEAR FLEX PLAN: FLN73XXX-11000UC</b> On-site parts and labor coverage for years 3 to 5Parts, electronics and UPS batteries coverage24x7 on-site labor coverage, next day responseNext day shippingTechnical support |



Powering Business Worldwide

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.