

Eaton 9PX 5kVA 120V Stepdown Transformer - 18 NEMA 5-20R Outlets, 60 Hz, L6-30P Input, 3 ft. Cord, 3U Rack/Tower

MODEL NUMBER: 9PXTFMR5



5kVA transformer converts UPS 208V input to 120V for powering low-voltage AC components.

Features

208V to 120V Isolation Transformer Converts High-Voltage Input to Low-Voltage Output

This 5kVA Stepdown Transformer converts your UPS system's 208V high-voltage input to 120V low-voltage output. It features 18 NEMA 5-20R outlets (two sets of nine outlets) for connecting equipment with common NEMA 5-15P and NEMA 5-20P plugs. Resettable 20A circuit breakers protect your 120V equipment against overload conditions. The 9PXTFMR5 works with Eaton's 9PX5K, 9PX6K, 9PX3K3UN and 8kVA to 11kVA 9PX UPS systems.

Versatile Installation Options

You can mount the 9PXTFMR5 in 3U of space in an EIA-standard 19-inch rack using the included 4-post rail kit or an optional 2-post rail kit (RK2PC, sold separately). You can also adapt it for tower installation using the included joining bracket and hardware. The three-foot power cord with L6-30P plug connects to a compatible AC outlet.

Highlights

- Converts 208V AC input into 120V output for powering low-voltage equipment
- 18 NEMA 5-20R 120V outlets for connecting components with 5-15P or 5-20P plugs
- Resettable circuit breakers protect mission-critical equipment from hazardous overloads
- 3 ft. power cord with L6-30P input plug connects to compatible AC source

System Requirements

Compatible with Eaton's 9PX5K, 9PX6K, 9PX3K3UN and 8kVA to 11kVA 9PX UPS systems

Package Includes

- 9PXTFMR5 5kVA 120V Stepdown Transformer
- Joining bracket and hardware for tower configuration
- Rack-mounting hardware
- Owner's manuals

Specifications

OVERVIEW	
UPC Code	743172039293
Accessory Type	Isolation Transformer
Accessory Class	UPS Accessories
INPUT	
UPS Input Connection Type	L6-30P
UPS Input Cord Length (ft.)	3



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States

UPS Input Cord Length (m)	0.9
Plug Type	L6-30P
Input Phase	Single-Phase
OUTPUT	
Output Receptacles	(18) 5-20R
Individually Controllable Load Banks	No
BATTERY	
Expandable Runtime	No
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	3U
Unit Dimensions (hwd / in.)	5.100 x 17.300 x 25.400
ENVIRONMENTAL	
Operating Temperature Range	0° to 40°C (32° to 104°F)
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico)
Product Compliance	CE (Europe); ENERGY STAR Qualified; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty



Powering Business Worldwide

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.