



Powering Business Worldwide

# 9PX G2 PowerPass Distribution Module for 3kVA to 6kVA 9PX G2 UPS Systems, L6-30P Input, 1x L6-30R, 1x L14-30R and 6x 5-20R Outlets, 3U Rack/Tower

MODEL NUMBER: 9PXPPDM1G2



Converts 208V UPS input to 120V for powering low-voltage AC components and transfers UPS power to utility during UPS maintenance or replacement.

## Features

### 208V to 120V Power Distribution Module Converts High-Voltage Input to Low-Voltage Output

The 9PXPPDM1G2 converts your UPS system's 208V high-voltage input to 120V low-voltage output. It features one L6-30R, one L14-30R and six NEMA 5-20R outlets for connecting equipment. Resettable 30A circuit breakers protect against overload conditions.

### Compatible with Select Eaton UPS Systems

The 9PXPPDM1G2 works with Eaton's 9PX5KG2, 9PX6KG2, 9PX6K-L and 9PX3K3UG2 UPS systems. Its front-panel maintenance bypass switch lets you service or replace the UPS system without powering down any equipment and risking costly downtime. All connected equipment remains energized, even while the UPS system is not present.

### Versatile Installation Options

You can mount the 9PXPPDM1G2 in 3U of space in an EIA-standard 19-inch rack using the included 4-post rail kit or an optional 2-post rail kit (RK2PC, sold separately). You can also adapt it for tower installation using the included joining bracket and hardware. The 10-foot power cord with L6-30P plug connects to a compatible AC outlet.

## Specifications

OVERVIEW	
UPC Code	786689876036
Accessory Type	Power Module
Accessory Class	UPS Accessories

## Highlights

- Converts high-voltage AC output into low voltage for powering low-voltage equipment
- Provides extra protection against power spikes and surges that can damage equipment
- Resettable circuit breakers protect connected equipment from hazardous overloads
- Maintenance bypass allows UPS service or replacement without powering down load

## System Requirements

Compatible with Eaton's 9PX5KG2, 9PX6KG2, 9PX6K-L and 9PX3K3UG2 UPS systems

## Package Includes

- 9PXPPDM1G2 PowerPass Distribution Module
- Joining bracket and hardware for tower configuration
- Rack-mounting hardware
- Owner's manuals



Powering Business Worldwide

<b>INPUT</b>	
Input Phase	Single-Phase
UPS Input Connection Type	L6-30P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Input Plug Type	NEMA L6-30P
<b>OUTPUT</b>	
Output Capacity (VA)	6000
Output Capacity (kVA)	6
Output Capacity (Watts)	6000
Output Capacity (kW)	6
Frequency Compatibility	50 / 60 Hz
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	100V; 110V; 120V; 208V; 220V; 230V; 240V
Output Receptacles	(6) 5-20R; (1) L14-30R; (1) L6-30R
Individually Controllable Load Banks	No
<b>BATTERY</b>	
Expandable Runtime	No
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount; Tower
Rack Height	3U
Unit Dimensions (hwd / in.)	5.100 x 17.300 x 25.040
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	NOM (Mexico); cUL Listed
Product Compliance	CE (Europe); ENERGY STAR Qualified; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.