



Powering Business Worldwide

# 9PX G2 10kVA 120V Step-Down Transformer - 8 NEMA 5-20R and 2 L14-30R Outlets, 50/60 Hz, Hardwire Input, 3U Rack/Tower

MODEL NUMBER: 9PXTFMR11G2



10kVA transformer converts UPS 208V input to 120V for powering low-voltage AC components.

## Features

### 208V to 120V Transformer Converts High-Voltage Input to Low-Voltage Output

This 10kVA Step-Down Transformer converts your UPS system's 208V high-voltage input to 120V low-voltage output. It features eight NEMA 5-20R and two L14-30R outlets for connecting equipment. Resettable circuit breakers protect your 120V equipment against overload conditions. The 9PXTFMR11G2 works with Eaton's 9PX8KG2 and 9PX11KG2 9PX G2 UPS systems.

### Versatile Installation Options

You can mount the 9PXTFMR11G2 in 3U of space in an EIA-standard 19-inch rack using the included 4-post rail kit or adapt it for tower installation using the included joining bracket and hardware. Cable glands are included for hardwire input.

## Specifications

OVERVIEW	
UPC Code	786689876029
Accessory Type	Isolation Transformer
Accessory Class	UPS Accessories
INPUT	
Input Phase	Single-Phase
UPS Input Connection Type	Hardwire
Input Plug Type	Hard-wire
OUTPUT	

## Highlights

- Converts 208V AC input into 120V output for powering low-voltage equipment
- 8 NEMA 5-20R and 2 L14-30R 120V outlets for connecting components
- Resettable circuit breakers protect mission-critical equipment from hazardous overloads
- Requires hardwired connection to Eaton 9PX8KG2 or 9PX11KG2 9PX G2 UPS systems

## System Requirements

Compatible with Eaton's 9PX8KG2 and 9PX11KG2 9PX G2 UPS systems

## Package Includes

- 9PXTFMR11G2 10kVA 120V Step-Down Transformer
- Hardwire cable
- (2) Cable glands
- Joining bracket and hardware for tower configuration
- Rack-mounting hardware
- Owner's manuals



Powering Business Worldwide

Output Capacity (VA)	10000
Output Capacity (kVA)	10
Output Capacity (Watts)	10000
Output Capacity (kW)	10
Frequency Compatibility	50 / 60 Hz
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	100V; 110V; 120V
Output Receptacles	(8) 5-20R; (2) L14-30R
Individually Controllable Load Banks	No
<b>BATTERY</b>	
Expandable Runtime	No
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount; Tower
Rack Height	3U
Unit Dimensions (hwd / in.)	5.120 x 17.300 x 27.400
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; NOM (Mexico)
Product Compliance	CE (Europe); ENERGY STAR Qualified; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Extended Service Plans	<b>ADVANCED DEPOT EXCHANGE</b> Service Part Number: 9SW5Y-11000UC Expedited parts coverage for 5 years Parts, electronics and UPS batteries coverage Next business day shipping Technical support <b>ON-SITE 24X7, NEXT DAY RESPONSE (US ONLY)</b> 2 YEAR UPGRADE: WUN72XXX-11000UC On-site expedited parts and labor coverage for first 2 years Parts, electronics and UPS batteries coverage Eaton on-site labor coverage 24x7 coverage, next day response Next day shipping Technical support <b>3 YEAR FLEX PLAN: FLN73XXX-11000UC</b> On-site parts and labor coverage for years 3 to 5 Parts, electronics and UPS batteries coverage 24x7 on-site labor coverage, next day response Next day shipping Technical support

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.