



Powering Business Worldwide

9PX G2 5kVA 120V Step-Down Transformer - 18 NEMA 5-20R Outlets, 60 Hz, L6-30P Input, 3 ft. Cord, 3U Rack/Tower

MODEL NUMBER: 9PXTFMR5G2



5kVA transformer converts UPS 208V input to 120V for powering low-voltage AC components.

Features

208V to 120V Transformer Converts High-Voltage Input to Low-Voltage Output

This 5kVA Step-Down Transformer converts your UPS system's 208V high-voltage input to 120V low-voltage output. It features 18 NEMA 5-20R outlets (two sets of nine outlets) for connecting equipment with common NEMA 5-15P and NEMA 5-20P plugs. Resettable 20A circuit breakers protect your 120V equipment against overload conditions. The 9PXTFMR5G2 works with Eaton's 9PX3K3UG2, 9PX5KG2, 9PX6KG2, 9PX6K-L, 9PX8KG2 and 9PX11KG2 9PX UPS systems.

Versatile Installation Options

You can mount the 9PXTFMR5G2 in 3U of space in an EIA-standard 19-inch rack using the included 4-post rail kit or an optional 2-post rail kit (RK2PC, sold separately). You can also adapt it for tower installation using the included joining bracket and hardware. The three-foot power cord with L6-30P plug connects to the L6-30R outlet on the UPS.

Specifications

OVERVIEW	
UPC Code	786689876012
Accessory Type	Isolation Transformer
Accessory Class	UPS Accessories
INPUT	
Input Phase	Single-Phase
UPS Input Connection Type	L6-30P
UPS Input Cord Length (ft.)	3

Highlights

- Converts 208V AC input into 120V output for powering low-voltage equipment
- 18 NEMA 5-20R 120V outlets for connecting components with 5-15P or 5-20P plugs
- Resettable circuit breakers protect mission-critical equipment from hazardous overloads
- 3 ft. power cord with L6-30P input plug connects to compatible UPS system

System Requirements

Compatible with Eaton's 9PX3K3UG2, 9PX5KG2, 9PX6KG2, 9PX6K-L, 9PX8KG2 and 9PX11KG2 9PX UPS systems

Package Includes

- 9PXTFMR5G2 5kVA 120V Step-Down Transformer
- Joining bracket and hardware for tower configuration
- Rack-mounting hardware
- Owner's manuals



Powering Business Worldwide

UPS Input Cord Length (m)	0.9
Input Plug Type	NEMA L6-30P
OUTPUT	
Output Capacity (VA)	5000
Output Capacity (kVA)	5
Output Capacity (Watts)	5000
Output Capacity (kW)	5
Frequency Compatibility	60 Hz
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	100V; 110V; 120V
Output Receptacles	(18) 5-20R
Individually Controllable Load Banks	No
BATTERY	
Expandable Runtime	No
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	3U
Unit Dimensions (hwd / in.)	5.100 x 17.300 x 25.040
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico)
Product Compliance	CE (Europe); ENERGY STAR Qualified; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.