

## Internet Office 120V 350VA 180W Standby UPS, Ultra-Compact Desktop, USB

MODEL NUMBER: **INTERNET350U**



### Description

Tripp Lite's INTERNET350U standby UPS system offers complete protection from blackouts, brownouts and transient surges on both AC and dialup modem lines. Provides seamless battery support during brownouts and power failures with enough runtime to save and shutdown connected equipment without data loss. Offers complete power protection in an ultra-compact, flat-pack housing with an appearance closer to a power strip than other bulky UPS designs. Includes 3 battery supported outlets for computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support. USB enables optional unattended system shutdown without data loss in the case of extended power failure. PowerAlert software available via free download, includes bundled USB cable. Built-in single line RJ11 phone suppression jacks with line splitter protects up to two directly connected modems, fax machines, cordless phones or other peripherals with a standard dialup phone connection. Built-in audible alarm and front panel LEDs offer continuous status information regarding line and battery power operation. 350VA/180 watt power handling ability supports entry-level PC systems for up to 12 minutes during power fail conditions. \$100,000 Ultimate Lifetime Insurance (USA, Puerto Rico, & Canada Only)

### Features

- INTERNET350U standby UPS offers complete protection from blackouts, brownouts and surges on both AC and TEL/DSL line connections
- 6 widely spaced outlets accommodate large transformer plugs without blocking outlets
- 3 battery supported outlets protect computer, monitor and vital system peripherals, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support
- Provides battery derived AC output during blackouts and brownouts
- 350VA/180 watt power handling ability supports a variety of PCs, workstations and other sensitive

### Highlights

- 350VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- USB, TEL/DSL protection, Wall mountable, 99% efficient
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

### Package Includes

- INTERNET350U UPS System
- USB cable
- Instruction manual



electronics

- Supports entry-level PC systems up to 12 minutes during blackout conditions
- Built-in single line TEL/DSL line surge suppression protects modems, fax machines or cordless phones on a single phone line connection
- Built-in USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [www.tripplite.com/poweralert](http://www.tripplite.com/poweralert)
- HID-compliant USB also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment - ideal for unattended kiosk applications
- Optional [PDUB15](#) bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Space saving, ultra-compact housing fits almost anywhere

## Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	350
Output Watt Capacity (Watts)	180
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(6) 5-15R
UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	
Rated input current (Maximum Load)	10A
Nominal Input Voltage(s) Supported	120V AC



UPS Input Connection Type	5-15P; Right-Angled
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
<b>BATTERY</b>	
Half Load Runtime (min.)	11.3 minutes (90w)
DC System Voltage (VDC)	12
Expandable Runtime	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Combination switch controls on/off power status and self-test operation
Audible Alarm	Audible alarm indicates power-failure and overload status
LED Indicators	2 LEDs indicate power status and overload/check battery status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	380 joules
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop
Primary Form Factor	Desktop
UPS Power Module Dimensions (hwd, in.)	3 x 8 x 6.4
UPS Power Module Dimensions (hwd, cm)	7.5 x 20.4 x 16.1
UPS Power Module Weight (lbs.)	5
UPS Power Module Weight (kg)	2.27
UPS Shipping Dimensions (hwd / in.)	4.1 x 11.3 x 7.7
UPS Shipping Dimensions (hwd / cm)	10.5 x 28.7 x 19.5
Shipping Weight (lbs.)	5.8
Shipping Weight (kg)	2.6
UPS Housing Material	ABS



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Primary UPS Height (mm)	76
Primary UPS Width (mm)	203
Primary UPS Depth (mm)	163
Shipping Height (mm)	104
Shipping Width (mm)	287
Shipping Depth (mm)	196
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	6
Battery Mode BTU / Hr. (Full Load)	92
AC Mode Efficiency Rating (100% Load)	99%
<b>COMMUNICATIONS</b>	
Communications Interface	USB (HID enabled)
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at <a href="http://www.tripplite.com/poweralert">http://www.tripplite.com/poweralert</a>
Communications Cable	RJ to USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at <a href="http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp+Lite">http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite</a>
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	4 milliseconds (AC to battery mode) / 2 milliseconds (Battery to AC mode)
Low Voltage Transfer to Battery Power (Setpoint)	99
High Voltage Transfer to Battery Power (Setpoint)	139
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>