

## 3.2-3.8kW Single-Phase Switched PDU, 200-240V Outlets (8 C13), C20 / L6-20P input, 8.5ft Cord, 1U Rack-Mount, TAA

MODEL NUMBER: PDUMH20HVNET



### Description

Tripp Lite single phase Switched PDU / Power Distribution Unit offers advanced network control and monitoring with the ability to turn on, turn off, recycle or lock-out power to each individual receptacle, monitor site electrical conditions and remotely monitor output power consumption. PowerAlert interface supports remote control and custom notification of user-specified conditions via email, secure web, SNMP, Telnet or SSH interface. Individually switched outlets can be controlled in real-time to remotely reboot unresponsive network hardware, or be custom programmed for user-defined power-up and power-down sequences to ensure proper startup of interdependent IT systems and prevent inrush-related overloads as network equipment is first energized. Unused PDU outlets can be electronically locked off to prevent the connection of unauthorized hardware. PDU output current consumption in amps is continuously displayed locally via visual meter and remotely via web/network interface to warn of potential overloads before critical IT mains or branch breakers trip.

### Features

- 16/20A 200/208/230/240V Switched Power Distribution Unit / PDU with built-in web/network interface (Agency derated to 16A continuous)
- C20 inlet; 8.5 ft. / 2.6m C20 power cable with L6-20P plug adapter
- 8 switched C13 outlets
- 1U horizontal rackmount form factor
- Supports power-on, power-off or reboot of each outlet on a real-time or programmable basis
- Enables reboot of locked equipment, custom power-on/power-off sequences, load-shedding of optional loads and disabling unused outlets
- Network interface provides PDU control and data regarding input voltage, frequency and loading

### Highlights

- Switched 16/20A 200-240V PDU, 1U Horizontal Rackmount format
- Reports voltage, frequency & loading information via ethernet interface
- Visual current meter, reversible housing
- C20 inlet; 8.5ft / 2.6m C20 input cable with L6-20P adapter
- 8 C13 switched outlets with cord retention brackets
- Temperature, humidity and contact-closure monitoring options
- TAA Compliant

### Package Includes

- Rackmount PDU
- Rack mounting brackets



information

- Digital display reports load level information in amps
- Supports user-specified alarm notification thresholds
- In-rack environmental reporting with optional ENVIROSENSE temperature / humidity sensor and rack access notification with up to 4 optional SRSWITCH door sensors
- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing
- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login via web browser
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Included cord retention brackets
- Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
PDU Type	Switched
OUTPUT	
Output Capacity Details	3.84kW (240V), 3.68kW (230V), 3.52kW (220V), 3.33kW (208V), 3.2kW (200V) / 16A total capacity; 12A (10A CE) max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) C13
Output Nominal Voltage	200; 208; 220; 230; 240
Overload Protection	n/a
Customized Load Management Receptacles	8 individually switched output receptacles
INPUT	
PDU Input Voltage	200; 208; 220; 230; 240



Recommended Electrical Service	20A 208/240V; 16A 230V
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Cord Length (ft.)	8.5
Input Cord Length (m)	2.6
Input Phase	Single-Phase
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Digital display reports total PDU output current in amps
Front Panel LEDs	8 LEDs display power on-off status for each output receptacle
Switches	n/a
<b>PHYSICAL</b>	
Minimum Required Rack Depth (inches)	17.1
Minimum Required Rack Depth (cm)	43.3
Shipping Dimensions (hwd / in.)	5.3 x 20.7 x 23.2
Shipping Dimensions (hwd / cm)	13.5 x 52.6 x 37.6
Shipping Weight (lbs.)	14.2
Shipping Weight (kg)	6.4
Unit Dimensions (hwd / in.)	1.75 x 17.3 x 14.8
Unit Dimensions (hwd / cm)	2.87 x 43.9 x 37.6
Unit Weight (lbs.)	9
Unit Weight (kg)	4.1
Material of Construction	Metal
Form Factors Supported	1U rackmount. Includes mounting accessories for 2-4 post racks
PDU Form Factor	1U; Horizontal
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
<b>COMMUNICATIONS</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

SNMP Compatibility	Yes, pre-installed <b>SNMPWEBCARD</b> provides remote monitoring via web, telnet, and SNMP management systems. Remote management gives user ability to turn connected loads on or off individually
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL 60950-1 (USA, Canada), Class A (Emissions), NOM (Mexico), , CE (IEC 60950), RoHS compliant, TAA compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>