

## SmartPro 230V 1kVA 900W Line-Interactive Sine Wave UPS, 2U Rack/Tower, Network Card Options, LCD, USB, DB9, 6 Outlets

MODEL NUMBER: **SMX1000RT2U**



### Description

The SMX1000RT2U SmartPro 230V 1kVA 900W Line-Interactive Sine Wave UPS provides battery backup and AC power protection against blackouts, brownouts, power surges and line noise that can damage electronics or destroy data. Ideal for backing up point-of-sale applications, VoIP systems and small business networks, the SMX1000RT2U switches to battery mode in milliseconds to keep your connected equipment running long enough to save files and shut down safely with no data loss.

Featuring six C13 outlets (four switchable) and a C14 inlet that accepts a user-supplied AC power cord, the SMX1000RT2U has an internal battery that provides 11.9 minutes of support at half load and 3.6 minutes at full load. A front-panel LCD screen lets you configure settings and monitor important data, such as load level, voltage, battery charge and estimated runtimes.

Automatic voltage regulation (AVR) maintains 230V nominal output over an input range of 182V to 278V without using battery power. EMI/RFI noise filtering improves your equipment's performance and prevents damage. A 350-joule surge suppression rating protects your equipment from harmful power surges. With Tripp Lite's free downloadable PowerAlert® software, the SMX1000RT2U enables safe unattended system shutdown and file saves in case of a prolonged power failure. Adding an optional Network Management Card permits remote management of the UPS.

### Features

Protects Mission-Critical Rack-Mounted Equipment

- Provides fully regulated sine wave AC output for point-of-sale applications, VoIP systems and small business networks
- Audible alarm signals loss of utility power, overload, low battery and fault conditions

### Highlights

- Corrects under- and overvoltages from 182V to 278V
- 6 C13 outlets—4 switchable via network interface
- Network power management and control capability
- Interactive LCD monitoring screen
- 11.9 min. runtime at half load; 3.6 min. at full load

### Package Includes

- SMX1000RT2U SmartPro 230V 1kVA 900W Line-Interactive Sine Wave UPS
- USB cable
- DB9 cable
- EPO cable
- (2) IEC-320 C13-to-C14 power cables
- Mounting hardware
- Owner's manual



- 6 C13 outlets
- C14 inlet accepts user-supplied AC power cord with country-specific plug
- 350-joule surge suppression rating

#### Reliable Battery Backup

- Supports half load up to 11.9 min. and full load up to 3.6 min.
- Internal batteries designed for hot-swap field replacement
- 97% line-power efficiency rating saves money in energy costs

#### 2 Load Banks with Switchable Outlets

- Can control 4 outlets remotely to reboot equipment or shed nonessential loads

#### Automatic Voltage Regulation (AVR)

- Maintains 230V nominal output over input range of 182V–278V without using battery power

#### EMI/RFI Line Noise Filtering

- Removes electromagnetic and radio frequency interference that can disrupt or damage equipment's performance

#### Interactive LCD Screen

- Front-panel LCD signals voltage, battery and load statuses
- Supports multiple advanced user setup and operating preferences
- Rotates for easy viewing in rack-mount or tower configurations

#### Optional Network Management Cards

- Compatible with Tripp Lite UPS management card options [TLNETCARD](#), [WEBCARDLX](#) and [SNMPWEBCARD](#)

#### Communications Ports

- USB and [DB9](#) ports enable data-saving unattended shutdown when used with Tripp Lite's Power Alert software (available via free download at [www.tripplite.com/poweralert](http://www.tripplite.com/poweralert))
- EPO port supports emergency shutdown in large facilities

#### Versatile Installation Options

- Hardware included for 4-post mounting in 2U of EIA-standard 19 in. rack
- Mounts on wall or 2-post rack with optional [2POSTRMKITWM](#) accessory
- Mounts in upright tower position with optional [2-9USTAND](#) accessory

## Specifications



MODEL TEXT	
Key Benefit	Protects connected mission-critical equipment against damage, downtime and data loss due to blackouts, brownouts, surges and line noise. Ideal solution for point-of-sale applications, VoIP systems and small business networks.
OUTPUT	
Output Volt Amp Capacity (VA)	1000
Output kVA Capacity (kVA)	1
Output Watt Capacity (Watts)	900
Power Factor	0.9
Nominal Output Voltage(s) Supported	220V; 230V; 240V
Nominal Voltage Details	230V nominal output in battery mode
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Line Mode)	+6%, -11%
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(6) C13
Included Output Power Cables	Includes 2 C13 to C14 output power cables
Load Management Receptacles	Two switchable two-outlet C13 load banks
Hot-Swap PDU options	PDUBHV10 (2U / 8 C13 outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
INPUT	
Rated input current (Maximum Load)	4.8A
Nominal Input Voltage(s) Supported	230V AC
UPS Input Connection Type	C14 inlet
UPS Input Connection Description	IEC320-C14 input connection accepts a variety of user supplied detachable C13 output cordsets to match country or site-specific power sources
Input Circuit Breakers	10A
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	3.6 min. (900w)



Half Load Runtime (min.)	11.9 min (450w)
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90% (typical, full load discharge)
Internal UPS Replacement Battery Cartridge	See Tripp Lite RBC selector guide
Battery Access	Front panel battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
Expandable Runtime	No
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 182 to 278
Overvoltage Correction	Input voltages between 244 and 278 are reduced by 12%
Undervoltage Correction	Input voltages between 182 and 206 are boosted by 12%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	350
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Included Mounting Accessory Description	4 post rackmount installation accessories included
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="#">2POSTRMKITWM</a> ); Wallmount ( <a href="#">2POSTRMKITWM</a> ); Tower ( <a href="#">2-9USTAND</a> ); 2-4 post front rail rackmount ( <a href="#">UPSHDEARKIT</a> )
Primary Form Factor	Rackmount
UPS Power Module Dimensions (hwd, in.)	3.5 x 17.5 x 13.5
UPS Power Module Dimensions (hwd, cm)	8.89 x 44.45 x 34.29



Rack Height (U Spaces)	2
Minimum Required Rack Depth (inches)	15.8
Minimum Required Rack Depth (cm)	40.13
UPS Power Module Weight (lbs.)	34
UPS Power Module Weight (kg)	15.42
UPS Shipping Dimensions (hwd / in.)	9 x 24 x 20.2
UPS Shipping Dimensions (hwd / cm)	22.86 x 60.96 x 51.31
Shipping Weight (lbs.)	36
Shipping Weight (kg)	16.3
Cooling Method	Fan
UPS Housing Material	Steel
Minimum Required Rack Depth (mm)	401
Primary UPS Height (mm)	89
Primary UPS Width (mm)	444
Primary UPS Depth (mm)	343
Shipping Height (mm)	229
Shipping Width (mm)	610
Shipping Depth (mm)	513
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	100
Battery Mode BTU / Hr. (Full Load)	918
AC Mode Efficiency Rating (100% Load)	97%
<b>COMMUNICATIONS</b>	
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)
Network Management Cards	SNMPWEBCARD; TLNETCARD; WEBCARDLX
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at <a href="http://www.tripplite.com/poweralert">http://www.tripplite.com/poweralert</a>



Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	182
High Voltage Transfer to Battery Power (Setpoint)	278
<b>SPECIAL FEATURES</b>	
Grounding Lug	Back panel grounding lug
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
<b>CERTIFICATIONS</b>	
UPS Certifications	CE; ROHS (Restriction of Hazardous Substances); Tested to GOST (Russia)
UPS Certification Details	IEC 62040-1, IEC 62040-2 Class A EMI
<b>WARRANTY</b>	
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>