

120V 1000VA 500W A/V Digital Line-Interactive UPS with LCD Status Screen, Tel/DSL/Coax Protection

MODEL NUMBER: HT1000UPS



Description

Tripp Lite's HT1000UPS Line-Interactive Digital UPS System offers voltage regulation, surge suppression and long-lasting battery support for personal computers, home entertainment systems and media centers. Internal UPS circuits support entry-level PCs for up to 60 minutes or individual VCR/DVR component for as long as 3 hours during power failures. Prevents data loss, viewing interruptions, lost recordings and loss of component programming. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 89 volts back to usable levels without consuming battery power. EMI/RFI line noise filtering improves component performance, assuring fuller audio and sharper video. Includes 4 battery-supported outlets, plus 4 surge suppression-only outlets for items not requiring battery support. USB port enables optional unattended system shutdown without data loss in the case of extended power failure. PowerAlert Software available via free download from www.tripplite.com. HID-compliant USB port also enables integration with built-in power management and auto-shutdown features of Windows and Mac OS X. Built-in single-line RJ-11 phone jacks provide surge protection for a modem, satellite receiver or other peripherals with a standard dialup/DSL phone connection. Two sets of 2.2 GHz coaxial jacks protect against surges entering on CATV, satellite or broadcast antenna connections. Built-in audible alarm and large LCD front panel voltage display indicates line power status, battery power status, battery low/replace status and voltage boost operation. 1000VA/500W power-handling ability supports media center PCs, home entertainment systems and audio/video components including flat-panel TVs, VCR/DVD players and PVRs (TiVo®). Offers 3 min. battery runtime with a full load of 1000VA/500W and 11 min. with a half load of 500VA/250W. \$100,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only).

Features

- LCD status screen indicates input voltage, battery capacity and a variety of operating conditions. Display is rotatable for easy viewing wwith UPS placed vertically or horizontally

Highlights

- Automatic voltage regulation protects sensitive A/V components from damaging power fluctuations
- Reliable battery support preserves settings and recordings through blackouts
- EMI/RFI line noise filtering improves component performance (fuller audio/sharper video)
- 8 widely spaced AC outlets (4 UPS/surge, 4 surge-only); USB port and FREE PowerAlert Software (Web download)
- 2-line 2.2 GHz cable/satellite/antenna coaxial surge protection plus single-line tel/DSL surge protection
- \$100,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)

Package Includes

- HT1000UPS Audio/Video Digital UPS System
- 1 phone and 2 gold coaxial cables
- Owner's manual with warranty information



- Offers automatic voltage regulation, surge suppression and long-lasting battery support during blackouts
- Supports entry-level PCs up to 60 min. or single VCR/DVR components for up to 3 hours during blackouts
- Regulates brownouts as low as 89V back to usable levels without using battery power
- 4 UPS battery-supported outlets plus 4 additional surge suppression-only outlets
- USB port enables unattended shutdown in the case of extended power failure
- HID-compliant USB port enables integration with built-in power management and auto-shutdown features of Windows and Mac OS X
- PowerAlert Software available via free download from www.tripplite.com
- Single-line phone suppression protects standard dialup/DSL phone connection
- 2-line 2.2 GHz coaxial surge protection for cable, satellite and antenna connections
- EMI/RFI line noise filtering improves component performance, assuring fuller audio and sharper video
- 1000VA/500W power handling ability supports a variety of sensitive computer, home theater and other equipment
- 3 min. full load runtime (1000VA/500W), 11 min. half load runtime (500VA/250W)
- Cabinet adapts to tower format or rackmount shelf format; 2U rackmount installation requires optional shelf, available separately
- Supports battery replacement via built-in access panel
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1000
Output Watt Capacity (Watts)	500
Nominal Output Voltage(s) Supported	115V; 120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	115V (+/- 5%)
Output Receptacles	(8) 5-15R
UPS Output Receptacles (Surge Suppression Only)	4 UPS outlets, 4 surge-only outlets
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave



INPUT	
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	3 min. (500w)
Half Load Runtime (min.)	11 min. (250w)
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	Less than 20 hours from 10% to 90%
Battery Access	Supports battery replacement via built-in access panel
Expandable Runtime	No
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 89
Undervoltage Correction	Input voltages between 89 and 104 are boosted by 14%
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Backlighted LCD screen indicates input voltage, 5-bar battery charge level, overload, AVR, on battery and replace battery status; LCD screen rotates for rack/tower viewing
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure, low-battery and overload status; alarm can be disabled using PowerAlert software
LED Indicators	Front panel LCD display
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); Coax jacks (2 sets)
UPS Dataline Suppression Details	HD-compatible 2.2GHz coaxial protection



EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Included Accessories	Tower
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	12 x 3.5 x 6.5
UPS Power Module Dimensions (hwd, cm)	30.5 x 8.9 x 16.5
UPS Power Module Weight (lbs.)	15.5
UPS Power Module Weight (kg)	7.03
UPS Shipping Dimensions (hwd / in.)	10.4 x 15.6 x 4.8
UPS Shipping Dimensions (hwd / cm)	26.5 x 39.5 x 12.3
Shipping Weight (lbs.)	15.8
Shipping Weight (kg)	7.2
UPS Housing Material	ABS
Primary UPS Height (mm)	305
Primary UPS Width (mm)	89
Primary UPS Depth (mm)	165
Shipping Height (mm)	264
Shipping Width (mm)	396
Shipping Depth (mm)	122
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	52.6
Battery Mode BTU / Hr. (Full Load)	536.8
AC Mode Efficiency Rating (100% Load)	97%
COMMUNICATIONS	
Communications Interface	USB (HID enabled)
PowerAlert Software	Free download from www.tripplite.com



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Communications Cable	USB cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	89
High Voltage Transfer to Battery Power (Setpoint)	139
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>