

SmartRack 6U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: **SRWF6U36**



Description

The SRWF6U36 SmartRack 6U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 150 pounds.

Because the low-profile cabinet mounts vertically, it extends less than 12 inches from the wall while housing equipment up to 36 inches deep, including 1U servers, UPS systems, battery packs and switches. In addition to 6U of rack space in the primary mounting area, it also includes a slide-out 2U mounting bracket at the top of the enclosure for patch panels up to 2.5 inches deep.

The top panel and front door lock securely to help prevent damage, tampering or theft. The cabinet is vented, which allows air to flow freely and keep equipment cool. The reversible front door can open left or right. Convenient top and bottom ports allow easy cable routing.

The SRWF6U36 comes fully assembled and ready to mount to the wall. Equipment installation is easy with threaded mounting holes and hardware that support M6 or 12-24 mounting.

Features

Saves Valuable Workspace

- Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way
- Houses EIA-standard 19 in. rack equipment in 6U of space
- Low-profile vertical-mount cabinet extends less than 12 in. from the wall while housing equipment up to

Highlights

- Maximum load capacity of 150 lb.
- Locking steel cabinet vented to keep equipment cool
- Secures 6U of 19 in. rack equipment up to 36 in. deep
- Includes additional 2U of space for patch panels
- Ships fully assembled for quick installation

Package Includes

- SRWF6U36 SmartRack 6U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet
- (12) M6 screws
- (12) M6 cup washers
- (12) 12-24 screws
- (2) Keys
- Owner's manual



36 in. deep, including 1U servers, UPS systems, battery packs and switches

- Also includes a slide-out 2U mounting bracket at the top of the enclosure for patch panels up to 2.5 in. deep
- Maximum load capacity of 150 lb.

Keeps Important Equipment Secure

- Top panel and reversible front door lock securely to help prevent damage, tampering or theft
- Front door latch also accommodates a user-supplied padlock for added security
- Vented cabinet keeps equipment cool
- Convenient ports with removable covers allow cable routing through top and bottom

Easy Enclosure and Equipment Installation

- Ships fully assembled for quick installation
- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Rails adjust easily—unscrew them, slide them to desired depth, and screw them back in
- Threaded mounting holes support M6 or 12-24 mounting
- Rack spaces marked for easy reference

Meets Payment Card Industry Standards

- Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

MODEL TEXT	
Key Benefit	Wall-mount cabinet secures and organizes 6U of 19-inch rack equipment in network wiring closets and other locations with limited floor space. Houses equipment up to 36 inches deep, but extends less than 12 inches from wall.
PHYSICAL	
Rack Height (U Spaces)	6
Maximum Device Depth (in.)	36
Maximum Device Depth (cm)	91.44
Minimum Device Depth (in.)	33
Minimum Device Depth (cm)	83.82
Shipping Dimensions (hwd / in.)	48.03 x 31.1 x 16.93
Shipping Dimensions (hwd / cm)	122 x 78.99 x 43
Shipping Weight (lbs.)	97



Shipping Weight (kg)	44
Unit Dimensions (hwd / in.)	43 x 25.6 x 11.5
Unit Dimensions (hwd / cm)	109.22 x 65.02 x 29.21
Unit Weight (lbs.)	88.2
Unit Weight (kg)	40.01
Color	Black
Weight Capacity - Stationary (lbs.)	150
Weight Capacity - Stationary (kg)	68
Maximum Device Depth (mm)	914
Minimum Device Depth (mm)	838
CERTIFICATIONS	
Certifications	EIA-310-E
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>