

Internet Office 120V 600VA 300W Standby UPS, Ultra-Compact Desktop, USB

MODEL NUMBER: **INTERNET600U**



Description

Ultra-compact standby UPS with built-in USB monitoring protects PCs, network workstations and other systems reliant upon a USB interface for UPS monitoring and unattended system shutdown. Maintains AC output during blackouts and brownouts starting at 99V. Includes USB monitoring with cabling, TEL/DSL line surge suppression, surge-only outlets and LED indicators. PowerAlert software available free via download.

Features

- INTERNET600U standby UPS offers protection from blackouts, brownouts and surges on both AC and dialup modem lines
- Provides seamless battery derived AC output during blackouts and severe brownouts so that connected equipment can be shut down without data loss
- USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- HID-compliant USB also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- 4 battery supported outlets protect computer, monitor and other vital system peripherals, plus 4 additional surge suppression-only outlets for printers and other system accessories not requiring battery support
- Attractive stealth black UPS color scheme
- Single line phone jacks with line splitter protects peripherals with a standard dialup phone line connection
- Audible alarm and front panel LEDs offer continuous status information regarding line and battery power

Highlights

- 600VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 4 UPS battery supported outlets, 4 surge-only outlets
- USB, TEL/DSL protection, Wall mountable, 99% efficient
- NEMA 5-15P input plug and 8 NEMA 5-15R outlets
- This product is ENERGY STAR qualified for its ability to save customers money while helping to protect the environment

Package Includes

- INTERNET600U UPS system
- USB cable
- Instruction manual



operation

- 600VA /300 watt power handling ability supports entry-level PC systems for several minutes during power fail conditions
- Includes attached 6 ft. AC power cord, on/off power switch
- Compatible with 120V/60 Hz applications in USA, Canada, Mexico and other countries
- Optional [PDUB15](#) bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- \$100,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	600
Output Watt Capacity (Watts)	300
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(8) 5-15R
UPS Output Receptacles (Surge Suppression Only)	4 UPS outlets, 4 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	
Rated input current (Maximum Load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P; Right-Angled
Input Circuit Breakers	10A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase



BATTERY	
Half Load Runtime (min.)	9.9 min. (150w)
DC System Voltage (VDC)	12
Expandable Runtime	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination switch controls on/off power status and self-test operation
Audible Alarm	Audible alarm indicates power-failure and overload status
LED Indicators	2 LEDs indicate power status and overload/check battery status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	420
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Included Mounting Accessory Description	Wallmount installation supported using keyhole mounting tabs
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop
Primary Form Factor	Desktop
UPS Power Module Dimensions (hwd, in.)	3.1 x 10.8 x 5.7
UPS Power Module Dimensions (hwd, cm)	7.87 x 27.43 x 14.48
UPS Power Module Weight (lbs.)	6.5
UPS Power Module Weight (kg)	2.95
UPS Shipping Dimensions (hwd / in.)	4.1 x 8 x 13
UPS Shipping Dimensions (hwd / cm)	10.41 x 20.32 x 33.02
Shipping Weight (lbs.)	7
Shipping Weight (kg)	3.2
UPS Housing Material	ABS
Primary UPS Height (mm)	79
Primary UPS Width (mm)	274



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Primary UPS Depth (mm)	145
Shipping Height (mm)	104
Shipping Width (mm)	203
Shipping Depth (mm)	330
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius.
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius.
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	14
Battery Mode BTU / Hr. (Full Load)	210
AC Mode Efficiency Rating (100% Load)	99%
COMMUNICATIONS	
Communications Interface	USB (HID enabled)
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	RJ to USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	99
High Voltage Transfer to Battery Power (Setpoint)	139
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); ENERGY STAR Qualified
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>