

7-Port Rugged Industrial USB 3.0 SuperSpeed Hub with 15KV ESD Immunity and Metal Case, Mountable

MODEL NUMBER: **U360-007-IND**



Description

Tripp Lite's U360-007-IND is a rugged, all metal, USB 3.0 SuperSpeed 7-Port hub that's ideal for use in data centers, work areas and industrial applications. Can be mounted on a wall or din rail with included mounting hardware. Supports SuperSpeed USB 3.0 transfer rates at 5 Gbps, but is also backward compatible to USB 2.0 and 1.1 (480mbps and 12mbps). It is bus-powered through the computer connection, or can self-power with an external adapter (not included) or via the included 3-wire terminal block connector (9-48V DC).

Features

- Increases the number of SuperSpeed USB 3.0 ports from a single computer port
- USB 3.0 compliant with data transfer rates up to 5 Gbps
- Backward-compatible with USB 2.0 and 1.x
- Rugged all-metal enclosure designed for use in industrial applications
- Wallmount and DIN rail hardware included for secure installation
- Three power connection options (source USB port, external power supply (* not included) or 3-wire terminal block)
- Each USB 3.0 port provides up to 900 mA of power
- Overcurrent detection and protection
- Supports 2 kV surge protection per port
- ESD protection to +/- 15 kV
- Automatic link and speed detection
- Plug-and-play; no software or drivers required

Highlights

- Increases the number of SuperSpeed USB 3.0 ports from a single computer port
- USB 3.0 compliant with data transfer rates up to 5 Gbps
- Rugged all-metal enclosure designed for use in industrial applications

System Requirements

- Compatible with all USB-enabled operating systems

Package Includes

- U360-007-IND Industrial-Grade USB 3.0 Hub
- USB 3.0 cable
- 3-pin power terminal block
- DIN mounting hardware
- Wallmount hardware
- Owner's Manual



Specifications

MODEL TEXT	
Key Benefit	Heavy Duty, Ruggedized USB 3.0 Hub for Industrial Applications
OVERVIEW	
Over Current Protection	Yes
PHYSICAL	
Unit Dimensions (hwd / in.)	5.6 x 2.5 x 1 in.
Unit Dimensions (hwd / cm)	14.224 x 6.35 x 2.54
Material of Construction	Metal
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Relative Humidity	5 to 95% RH
Operating Temperature	0°C to 60°C (32°F to 140°F)
CONNECTIONS	
Ports	7
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(7) USB 3.0 A (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>